

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211107

Luminaire Tested: **LSR4B15D010BZ EC4B10208027 4LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211107
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10208027 4LBPSMW1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1525.3 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211107

CATALOG NUMBER: LSR4B15D010BZ EC4B10208027 4LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P211107

CATALOG NUMBER: LSR4B15D010BZ EC4B10208027 4LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211107

CATALOG NUMBER: LSR4B15D010BZ EC4B10208027 4LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.2	3.8
10°-20°	166.0	10.9
20°-30°	250.0	16.4
30°-40°	297.5	19.5
40°-50°	296.9	19.5
50°-60°	241.5	15.8
60°-70°	148.5	9.7
70°-80°	57.5	3.8
80°-90°	9.2	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	474.2	31.1
0°-40°	771.7	50.6
0°-60°	1310.0	85.9
0°-90°	1525.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1525.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	615	
5°	613	58
15°	589	166
25°	544	250
35°	476	297
45°	386	297
55°	270	241
65°	149	149
75°	52	58
85°	7	9
90°	0	



TEST NUMBER: P211107

CATALOG NUMBER: LSR4B15D010BZ EC4B10208027 4LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	614.6
2.5°	615.5
5°	612.8
7.5°	609.1
10°	604.6
12.5°	596.5
15°	589.3
17.5°	578.4
20°	566.7
22.5°	555.8
25°	544.1
27.5°	527.8
30°	511.5
32.5°	496.2
35°	476.3
37.5°	454.6
40°	434.7
42.5°	410.3
45°	385.9
47.5°	359.7
50°	331.7
52.5°	302.8
55°	270.2
57.5°	238.6
60°	207.9
62.5°	178.0
65°	149.1
67.5°	122.0
70°	96.7
72.5°	73.2
75°	52.4
77.5°	34.3
80°	20.8
82.5°	12.7
85°	7.2
87.5°	3.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)