

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212105

Luminaire Tested: **LSR4B30D010BZ EC4B30508040 4LBWMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P212105  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B30D010BZ EC4B30508040 4LBWMW1  
Description: PORTFOLIO 4 INCH CYLINDER  
WIDE DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2640.1 lumens  
Efficiency: N/A  
Efficacy: 94.3 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P212105

CATALOG NUMBER: LSR4B30D010BZ EC4B30508040 4LBWMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P212105

CATALOG NUMBER: LSR4B30D010BZ EC4B30508040 4LBWMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																											
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78																											
3	96	87	80	75	93	85	79	74	83	77	73	80	76	72	78	74	71	69																											
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61																											
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55																											
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	60	55	51	50																											
7	73	61	53	48	71	60	53	48	59	52	47	57	51	47	56	51	47	45																											
8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41																											
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38																											
10	61	49	42	37	59	48	41	37	47	41	37	46	41	37	46	40	36	35																											

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P212105

CATALOG NUMBER: LSR4B30D010BZ EC4B30508040 4LBWMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	150.2	5.7
10°-20°	420.0	15.9
20°-30°	593.6	22.5
30°-40°	575.0	21.8
40°-50°	388.0	14.7
50°-60°	240.8	9.1
60°-70°	161.0	6.1
70°-80°	88.1	3.3
80°-90°	23.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1163.9	44.1
0°-40°	1738.9	65.9
0°-60°	2367.7	89.7
0°-90°	2640.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2640.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1600	
5°	1586	150
15°	1490	420
25°	1302	594
35°	925	575
45°	497	388
55°	264	241
65°	161	161
75°	82	88
85°	21	23
90°	0	



TEST NUMBER: P212105

CATALOG NUMBER: LSR4B30D010BZ EC4B30508040 4LBWMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1599.8
2.5°	1599.8
5°	1586.1
7.5°	1568.9
10°	1548.4
12.5°	1527.8
15°	1490.1
17.5°	1459.3
20°	1407.9
22.5°	1356.5
25°	1301.7
27.5°	1226.4
30°	1144.2
32.5°	1038.0
35°	924.9
37.5°	811.9
40°	698.8
42.5°	585.8
45°	496.7
47.5°	414.5
50°	352.8
52.5°	301.5
55°	263.8
57.5°	232.9
60°	209.0
62.5°	185.0
65°	161.0
67.5°	140.5
70°	119.9
72.5°	102.8
75°	82.2
77.5°	65.1
80°	48.0
82.5°	34.3
85°	20.6
87.5°	6.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)