

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211108

Luminaire Tested: **LSR4B15D010BZ EC4B10208027 4LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211108
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10208027 4LBSB1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1235.0 lumens
Efficiency: N/A
Efficacy: 86.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211108

CATALOG NUMBER: LSR4B15D010BZ EC4B10208027 4LBSB1

Luminous Intensity Polar Plot





TEST NUMBER: P211108

CATALOG NUMBER: LSR4B15D010BZ EC4B10208027 4LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88				88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76				76
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65				65
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57				57
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50				50
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44				44
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39				39
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35				35
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32				32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29				29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211108

CATALOG NUMBER: LSR4B15D010BZ EC4B10208027 4LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.4	4.2
10°-20°	145.9	11.8
20°-30°	217.0	17.6
30°-40°	252.6	20.4
40°-50°	246.2	19.9
50°-60°	189.3	15.3
60°-70°	104.7	8.5
70°-80°	27.7	2.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	414.3	33.5
0°-40°	666.9	54.0
0°-60°	1102.4	89.3
0°-90°	1235.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1235.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	545	
5°	542	51
15°	517	146
25°	471	217
35°	406	253
45°	319	246
55°	211	189
65°	105	105
75°	24	28
85°	0	0
90°	0	



TEST NUMBER: P211108

CATALOG NUMBER: LSR4B15D010BZ EC4B10208027 4LBSB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	544.8
2.5°	544.8
5°	541.7
7.5°	537.0
10°	533.8
12.5°	524.4
15°	516.6
17.5°	508.8
20°	497.8
22.5°	486.9
25°	471.2
27.5°	455.6
30°	439.9
32.5°	422.7
35°	405.5
37.5°	383.5
40°	364.8
42.5°	344.4
45°	319.4
47.5°	295.9
50°	269.3
52.5°	241.1
55°	211.3
57.5°	183.2
60°	156.6
62.5°	129.9
65°	104.9
67.5°	81.4
70°	59.5
72.5°	40.7
75°	23.5
77.5°	11.0
80°	1.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)