

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211143

Luminaire Tested: **LSR4B15D010BZ EC4B10209027 4LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211143
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10209027 4LBSWMH1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1223.0 lumens
Efficiency: N/A
Efficacy: 85.5 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211143

CATALOG NUMBER: LSR4B15D010BZ EC4B10209027 4LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P211143

CATALOG NUMBER: LSR4B15D010BZ EC4B10209027 4LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90																			
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79																			
3	96	88	82	76	94	87	81	76	84	79	74	81	77	73	79	75	72	70																			
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62																			
5	83	73	65	59	82	72	64	59	70	63	59	68	62	58	66	61	57	56																			
6	78	66	59	53	76	65	58	53	64	57	53	62	57	52	61	56	52	50																			
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45																			
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41																			
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	49	43	39	38																			
10	60	48	41	37	59	48	41	37	47	41	36	46	40	36	45	40	36	35																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211143

CATALOG NUMBER: LSR4B15D010BZ EC4B10209027 4LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.6	5.9
10°-20°	189.9	15.5
20°-30°	255.0	20.8
30°-40°	261.0	21.3
40°-50°	225.9	18.5
50°-60°	150.3	12.3
60°-70°	61.7	5.0
70°-80°	7.3	0.6
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	516.5	42.2
0°-40°	777.5	63.6
0°-60°	1153.7	94.3
0°-90°	1223.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1223.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	775	
5°	763	72
15°	678	190
25°	556	255
35°	417	261
45°	294	226
55°	167	150
65°	61	62
75°	3	7
85°	0	0
90°	0	



TEST NUMBER: P211143

CATALOG NUMBER: LSR4B15D010BZ EC4B10209027 4LBSWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	775.2
2.5°	773.6
5°	763.2
7.5°	747.1
10°	725.5
12.5°	701.4
15°	678.2
17.5°	648.5
20°	619.7
22.5°	589.2
25°	556.3
27.5°	521.1
30°	485.8
32.5°	450.5
35°	416.8
37.5°	384.8
40°	354.3
42.5°	323.9
45°	294.2
47.5°	262.9
50°	230.9
52.5°	198.8
55°	166.7
57.5°	138.7
60°	109.8
62.5°	83.4
65°	60.9
67.5°	40.1
70°	23.2
72.5°	11.2
75°	3.2
77.5°	1.6
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)