

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212108

Luminaire Tested: **LSR4B30D010BZ EC4B30509040 4LBCSMMS1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212108
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30509040 4LBCSMMS1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2232.5 lumens
Efficiency: N/A
Efficacy: 79.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212108

CATALOG NUMBER: LSR4B30D010BZ EC4B30509040 4LBCSMMS1

Luminous Intensity Polar Plot





TEST NUMBER: P212108

CATALOG NUMBER: LSR4B30D010BZ EC4B30509040 4LBCSMMS1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76			76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65			65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57			57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50			50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44			44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40			40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36			36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32			32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29			29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212108

CATALOG NUMBER: LSR4B30D010BZ EC4B30509040 4LBCSMMS1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.6	4.3
10°-20°	271.1	12.1
20°-30°	396.0	17.7
30°-40°	452.9	20.3
40°-50°	435.3	19.5
50°-60°	336.1	15.1
60°-70°	187.6	8.4
70°-80°	54.6	2.4
80°-90°	2.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	763.7	34.2
0°-40°	1216.6	54.5
0°-60°	1988.0	89.0
0°-90°	2232.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2232.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1025	
5°	1017	97
15°	962	271
25°	861	396
35°	725	453
45°	568	435
55°	377	336
65°	188	188
75°	48	55
85°	1	2
90°	0	



TEST NUMBER: P212108

CATALOG NUMBER: LSR4B30D010BZ EC4B30509040 4LBCSMMS1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1025.2
2.5°	1025.2
5°	1016.6
7.5°	1012.2
10°	997.8
12.5°	980.5
15°	961.7
17.5°	942.9
20°	915.5
22.5°	893.8
25°	860.6
27.5°	827.4
30°	794.2
32.5°	761.0
35°	724.9
37.5°	688.8
40°	646.9
42.5°	609.4
45°	567.5
47.5°	519.8
50°	475.1
52.5°	426.0
55°	376.9
57.5°	326.3
60°	278.7
62.5°	231.0
65°	187.7
67.5°	147.3
70°	109.7
72.5°	76.5
75°	47.7
77.5°	24.5
80°	8.7
82.5°	2.9
85°	1.4
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)