

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212111

Luminaire Tested: **LSR4B30D010BZ EC4B30509040 4LBMGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212111
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30509040 4LBMGPH1
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1367.1 lumens
Efficiency: N/A
Efficacy: 48.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.92
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212111

CATALOG NUMBER: LSR4B30D010BZ EC4B30509040 4LBMGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P212111

CATALOG NUMBER: LSR4B30D010BZ EC4B30509040 4LBMGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93		
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	88	86		
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79		
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73		
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68		
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63		
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59		
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55		
9	73	63	57	53	72	63	57	53	62	57	53	61	56	53	60	56	52	51		
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	52	49	48		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212111

CATALOG NUMBER: LSR4B30D010BZ EC4B30509040 4LBMGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.3	9.5
10°-20°	337.3	24.7
20°-30°	432.6	31.6
30°-40°	312.7	22.9
40°-50°	112.1	8.2
50°-60°	30.3	2.2
60°-70°	9.9	0.7
70°-80°	3.0	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	899.1	65.8
0°-40°	1211.8	88.6
0°-60°	1354.2	99.1
0°-90°	1367.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1367.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1406	
5°	1380	129
15°	1201	337
25°	954	433
35°	500	313
45°	135	112
55°	32	30
65°	9	10
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P212111

CATALOG NUMBER: LSR4B30D010BZ EC4B30509040 4LBMGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1405.5
2.5°	1399.7
5°	1379.6
7.5°	1348.0
10°	1304.9
12.5°	1256.0
15°	1201.4
17.5°	1146.8
20°	1092.2
22.5°	1029.0
25°	954.2
27.5°	868.0
30°	758.8
32.5°	632.3
35°	500.1
37.5°	379.4
40°	275.9
42.5°	195.4
45°	135.1
47.5°	92.0
50°	60.4
52.5°	43.1
55°	31.6
57.5°	23.0
60°	17.2
62.5°	14.4
65°	8.6
67.5°	5.7
70°	5.7
72.5°	2.9
75°	2.9
77.5°	2.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)