

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212117

Luminaire Tested: **LSR4B30D010BZ EC4B30509040 4LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212117
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30509040 4LBNGPH1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1186.2 lumens
Efficiency: N/A
Efficacy: 42.4 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.88
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212117

CATALOG NUMBER: LSR4B30D010BZ EC4B30509040 4LBNGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P212117

CATALOG NUMBER: LSR4B30D010BZ EC4B30509040 4LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94		
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87		
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81		
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76		
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70		
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66		
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62		
8	80	70	64	60	78	70	64	60	68	63	60	67	63	59	66	62	59	58		
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54		
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	52	51		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212117

CATALOG NUMBER: LSR4B30D010BZ EC4B30509040 4LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.3	10.9
10°-20°	324.2	27.3
20°-30°	395.1	33.3
30°-40°	260.7	22.0
40°-50°	60.0	5.1
50°-60°	11.5	1.0
60°-70°	4.2	0.4
70°-80°	1.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	848.6	71.5
0°-40°	1109.3	93.5
0°-60°	1180.8	99.5
0°-90°	1186.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1186.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1422	
5°	1388	129
15°	1161	324
25°	868	395
35°	417	261
45°	66	60
55°	12	11
65°	3	4
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P212117

CATALOG NUMBER: LSR4B30D010BZ EC4B30509040 4LBNGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1422.5
2.5°	1419.6
5°	1388.0
7.5°	1344.9
10°	1287.4
12.5°	1229.9
15°	1161.0
17.5°	1089.1
20°	1014.4
22.5°	948.3
25°	867.8
27.5°	787.4
30°	683.9
32.5°	557.5
35°	416.7
37.5°	290.2
40°	186.8
42.5°	114.9
45°	66.1
47.5°	34.5
50°	20.1
52.5°	17.2
55°	11.5
57.5°	8.6
60°	8.6
62.5°	5.7
65°	2.9
67.5°	2.9
70°	2.9
72.5°	2.9
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)