

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212131

Luminaire Tested: **LSR4B30D010BZ EC4B30509040 4LBWGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P212131  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B30D010BZ EC4B30509040 4LBWGPH1  
Description: PORTFOLIO 4 INCH CYLINDER  
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1657.2 lumens  
Efficiency: N/A  
Efficacy: 59.2 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P212131  
CATALOG NUMBER: LSR4B30D010BZ EC4B30509040 4LBWGPH1

### Luminous Intensity Polar Plot





TEST NUMBER: P212131

CATALOG NUMBER: LSR4B30D010BZ EC4B30509040 4LBWGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92			
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	77	76			
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69			
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			
6	83	72	65	61	81	71	65	60	70	64	60	68	63	59	67	63	59	57			
7	78	67	60	55	76	66	60	55	65	59	55	64	58	55	63	58	54	53			
8	73	62	56	51	72	62	55	51	61	55	51	59	54	50	58	54	50	48			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45			
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P212131

CATALOG NUMBER: LSR4B30D010BZ EC4B30509040 4LBWGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	112.5	6.8
10°-20°	318.8	19.2
20°-30°	457.3	27.6
30°-40°	430.5	26.0
40°-50°	237.8	14.3
50°-60°	76.3	4.6
60°-70°	19.1	1.2
70°-80°	4.5	0.3
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	888.6	53.6
0°-40°	1319.1	79.6
0°-60°	1633.2	98.6
0°-90°	1657.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1657.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1193	
5°	1187	113
15°	1130	319
25°	1003	457
35°	698	431
45°	302	238
55°	78	76
65°	17	19
75°	3	5
85°	0	0
90°	0	



TEST NUMBER: P212131

CATALOG NUMBER: LSR4B30D010BZ EC4B30509040 4LBWGPH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1192.7
2.5°	1184.1
5°	1187.0
7.5°	1178.4
10°	1164.0
12.5°	1149.6
15°	1129.5
17.5°	1112.3
20°	1083.5
22.5°	1043.3
25°	1003.1
27.5°	948.5
30°	876.6
32.5°	796.1
35°	698.4
37.5°	594.9
40°	488.6
42.5°	390.9
45°	301.8
47.5°	227.1
50°	163.8
52.5°	115.0
55°	77.6
57.5°	51.7
60°	37.4
62.5°	25.9
65°	17.2
67.5°	11.5
70°	8.6
72.5°	5.7
75°	2.9
77.5°	2.9
80°	2.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)