

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211201

Luminaire Tested: **LSR4B15D010BZ EC4B10208030 4LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211201
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10208030 4LBSWMH1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1488.7 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211201

CATALOG NUMBER: LSR4B15D010BZ EC4B10208030 4LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P211201

CATALOG NUMBER: LSR4B15D010BZ EC4B10208030 4LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90			
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79			
3	96	88	82	76	94	87	81	76	84	79	74	81	77	73	79	75	72	70			
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62			
5	83	73	65	59	82	72	64	59	70	63	59	68	62	58	66	61	57	56			
6	78	66	59	53	76	65	58	53	64	57	53	62	57	52	61	56	52	50			
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45			
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41			
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	49	43	39	38			
10	60	48	41	37	59	48	41	37	47	41	36	46	40	36	45	40	36	35			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211201

CATALOG NUMBER: LSR4B15D010BZ EC4B10208030 4LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.2	5.9
10°-20°	231.1	15.5
20°-30°	310.3	20.8
30°-40°	317.7	21.3
40°-50°	275.0	18.5
50°-60°	182.9	12.3
60°-70°	75.1	5.0
70°-80°	9.0	0.6
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	628.6	42.2
0°-40°	946.3	63.6
0°-60°	1404.2	94.3
0°-90°	1488.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1488.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	944	
5°	929	87
15°	825	231
25°	677	310
35°	507	318
45°	358	275
55°	203	183
65°	74	75
75°	4	9
85°	0	0
90°	0	



TEST NUMBER: P211201

CATALOG NUMBER: LSR4B15D010BZ EC4B10208030 4LBSWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	943.5
2.5°	941.5
5°	928.9
7.5°	909.3
10°	883.0
12.5°	853.7
15°	825.4
17.5°	789.3
20°	754.2
22.5°	717.1
25°	677.1
27.5°	634.2
30°	591.3
32.5°	548.3
35°	507.4
37.5°	468.3
40°	431.3
42.5°	394.2
45°	358.1
47.5°	320.0
50°	281.0
52.5°	242.0
55°	202.9
57.5°	168.8
60°	133.7
62.5°	101.5
65°	74.2
67.5°	48.8
70°	28.3
72.5°	13.7
75°	3.9
77.5°	2.0
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)