

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212135

Luminaire Tested: **LSR4B30D010BZ EC4B30509040 4LBWWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P212135  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B30D010BZ EC4B30509040 4LBWWH1  
Description: PORTFOLIO 4 INCH CYLINDER  
WIDE DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2197.1 lumens  
Efficiency: N/A  
Efficacy: 78.5 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P212135

CATALOG NUMBER: LSR4B30D010BZ EC4B30509040 4LBWWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P212135

CATALOG NUMBER: LSR4B30D010BZ EC4B30509040 4LBWWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92				92															
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	85	84				84															
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76				76															
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69				69															
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63				63															
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58				58															
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53				53															
8	73	62	56	51	72	62	55	51	61	55	51	60	54	50	59	54	50	49				49															
9	69	58	51	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45				45															
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41				41															

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P212135

CATALOG NUMBER: LSR4B30D010BZ EC4B30509040 4LBWWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	133.1	6.1
10°-20°	411.8	18.7
20°-30°	633.4	28.8
30°-40°	611.1	27.8
40°-50°	318.6	14.5
50°-60°	67.1	3.1
60°-70°	15.6	0.7
70°-80°	6.0	0.3
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1178.3	53.6
0°-40°	1789.4	81.4
0°-60°	2175.1	99.0
0°-90°	2197.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2197.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1374	
5°	1385	133
15°	1457	412
25°	1388	633
35°	992	611
45°	405	319
55°	60	67
65°	14	16
75°	6	6
85°	0	0
90°	0	



TEST NUMBER: P212135

CATALOG NUMBER: LSR4B30D010BZ EC4B30509040 4LBWWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1373.7
2.5°	1376.6
5°	1385.2
7.5°	1396.7
10°	1414.0
12.5°	1437.0
15°	1457.1
17.5°	1468.6
20°	1460.0
22.5°	1442.7
25°	1388.1
27.5°	1322.0
30°	1235.8
32.5°	1120.8
35°	991.5
37.5°	850.7
40°	704.1
42.5°	557.5
45°	405.2
47.5°	273.0
50°	175.3
52.5°	106.3
55°	60.4
57.5°	37.4
60°	25.9
62.5°	20.1
65°	14.4
67.5°	11.5
70°	8.6
72.5°	8.6
75°	5.7
77.5°	2.9
80°	2.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)