

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211209

Luminaire Tested: **LSR4B15D010BZ EC4B10209030 4LBCSMMS1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211209
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10209030 4LBCSMMS1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1126.1 lumens
Efficiency: N/A
Efficacy: 78.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211209

CATALOG NUMBER: LSR4B15D010BZ EC4B10209030 4LBCSMMS1

Luminous Intensity Polar Plot





TEST NUMBER: P211209

CATALOG NUMBER: LSR4B15D010BZ EC4B10209030 4LBCSMMS1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88	88	88	88
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76	76	76	76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65	65	65	65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57	57	57	57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50	50	50	50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44	44	44	44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40	40	40	40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36	36	36	36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32	32	32	32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29	29	29	29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211209

CATALOG NUMBER: LSR4B15D010BZ EC4B10209030 4LBCSMMS1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.7	4.3
10°-20°	136.8	12.1
20°-30°	199.7	17.7
30°-40°	228.4	20.3
40°-50°	219.6	19.5
50°-60°	169.5	15.1
60°-70°	94.6	8.4
70°-80°	27.5	2.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	385.2	34.2
0°-40°	613.7	54.5
0°-60°	1002.8	89.0
0°-90°	1126.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1126.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	517	
5°	513	49
15°	485	137
25°	434	200
35°	366	228
45°	286	220
55°	190	170
65°	95	95
75°	24	28
85°	1	1
90°	0	



TEST NUMBER: P211209

CATALOG NUMBER: LSR4B15D010BZ EC4B10209030 4LBCSMMS1

CANDELA DISTRIBUTION (FULL):

	0°
0°	517.1
2.5°	517.1
5°	512.8
7.5°	510.6
10°	503.3
12.5°	494.6
15°	485.1
17.5°	475.6
20°	461.8
22.5°	450.9
25°	434.1
27.5°	417.4
30°	400.6
32.5°	383.9
35°	365.6
37.5°	347.4
40°	326.3
42.5°	307.4
45°	286.3
47.5°	262.2
50°	239.6
52.5°	214.9
55°	190.1
57.5°	164.6
60°	140.6
62.5°	116.5
65°	94.7
67.5°	74.3
70°	55.4
72.5°	38.6
75°	24.0
77.5°	12.4
80°	4.4
82.5°	1.5
85°	0.7
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)