

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212155

Luminaire Tested: **LSR4B30D010BZ EC4B30508050 4LBSLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P212155  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B30D010BZ EC4B30508050 4LBSLI1  
Description: PORTFOLIO 4 INCH CYLINDER  
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3094.2 lumens  
Efficiency: N/A  
Efficacy: 110.5 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P212155

CATALOG NUMBER: LSR4B30D010BZ EC4B30508050 4LBSLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P212155

CATALOG NUMBER: LSR4B30D010BZ EC4B30508050 4LBSLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90																			
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80																			
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71																			
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63																			
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57																			
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51																			
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46																			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42																			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39																			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P212155

CATALOG NUMBER: LSR4B30D010BZ EC4B30508050 4LBSLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	200.3	6.5
10°-20°	510.9	16.5
20°-30°	662.1	21.4
30°-40°	648.7	21.0
40°-50°	549.8	17.8
50°-60°	360.4	11.6
60°-70°	144.9	4.7
70°-80°	16.6	0.5
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1373.3	44.4
0°-40°	2022.0	65.3
0°-60°	2932.3	94.8
0°-90°	3094.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3094.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2209	
5°	2151	200
15°	1822	511
25°	1446	662
35°	1031	649
45°	716	550
55°	401	360
65°	140	145
75°	7	17
85°	0	0
90°	0	



TEST NUMBER: P212155

CATALOG NUMBER: LSR4B30D010BZ EC4B30508050 4LBSLI1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2209.4
2.5°	2192.2
5°	2151.1
7.5°	2082.6
10°	1997.0
12.5°	1904.5
15°	1822.3
17.5°	1733.2
20°	1644.2
22.5°	1548.3
25°	1445.5
27.5°	1339.3
30°	1229.7
32.5°	1127.0
35°	1031.0
37.5°	952.3
40°	866.6
42.5°	791.3
45°	715.9
47.5°	637.1
50°	558.3
52.5°	479.6
55°	400.8
57.5°	328.8
60°	260.3
62.5°	198.7
65°	140.4
67.5°	92.5
70°	54.8
72.5°	24.0
75°	6.9
77.5°	3.4
80°	3.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)