

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212180

Luminaire Tested: **LSR4B30D010BZ EC4B30509050 4LBPSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P212180  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B30D010BZ EC4B30509050 4LBPSMW1  
Description: PORTFOLIO 4 INCH CYLINDER  
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2711.6 lumens  
Efficiency: N/A  
Efficacy: 96.8 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P212180

CATALOG NUMBER: LSR4B30D010BZ EC4B30509050 4LBPSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P212180

CATALOG NUMBER: LSR4B30D010BZ EC4B30509050 4LBPSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63			
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P212180

CATALOG NUMBER: LSR4B30D010BZ EC4B30509050 4LBPSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	103.5	3.8
10°-20°	295.1	10.9
20°-30°	444.4	16.4
30°-40°	528.8	19.5
40°-50°	527.8	19.5
50°-60°	429.3	15.8
60°-70°	264.1	9.7
70°-80°	102.3	3.8
80°-90°	16.4	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	843.0	31.1
0°-40°	1371.8	50.6
0°-60°	2328.8	85.9
0°-90°	2711.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2711.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1092	
5°	1089	104
15°	1048	295
25°	967	444
35°	847	529
45°	686	528
55°	480	429
65°	265	264
75°	93	102
85°	13	16
90°	0	



TEST NUMBER: P212180

CATALOG NUMBER: LSR4B30D010BZ EC4B30509050 4LBPSMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1092.5
2.5°	1094.1
5°	1089.3
7.5°	1082.9
10°	1074.8
12.5°	1060.4
15°	1047.5
17.5°	1028.2
20°	1007.4
22.5°	988.1
25°	967.2
27.5°	938.3
30°	909.4
32.5°	882.0
35°	846.7
37.5°	808.1
40°	772.8
42.5°	729.4
45°	686.0
47.5°	639.4
50°	589.6
52.5°	538.2
55°	480.4
57.5°	424.2
60°	369.5
62.5°	316.5
65°	265.1
67.5°	216.9
70°	171.9
72.5°	130.1
75°	93.2
77.5°	61.1
80°	37.0
82.5°	22.5
85°	12.9
87.5°	6.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)