

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212206

Luminaire Tested: **LSR4B40D010BZ EC4B30509024 4LBNI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212206
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B40D010BZ EC4B30509024 4LBNI1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2174.2 lumens
Efficiency: N/A
Efficacy: 52.0 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212206

CATALOG NUMBER: LSR4B40D010BZ EC4B30509024 4LBNLI1

Luminous Intensity Polar Plot





TEST NUMBER: P212206

CATALOG NUMBER: LSR4B40D010BZ EC4B30509024 4LBNLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100										100																		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95										95																		
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90										90																		
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85										85																		
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81										81																		
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77										77																		
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73										73																		
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69										69																		
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66										66																		
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63										63																		
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61										61																		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212206

CATALOG NUMBER: LSR4B40D010BZ EC4B30509024 4LBNLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	440.9	20.3
10°-20°	754.9	34.7
20°-30°	600.0	27.6
30°-40°	317.6	14.6
40°-50°	54.7	2.5
50°-60°	4.1	0.2
60°-70°	2.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1795.8	82.6
0°-40°	2113.4	97.2
0°-60°	2172.2	99.9
0°-90°	2174.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2174.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5595	
5°	5016	441
15°	2729	755
25°	1292	600
35°	502	318
45°	57	55
55°	3	4
65°	3	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P212206

CATALOG NUMBER: LSR4B40D010BZ EC4B30509024 4LBNLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	5595.3
2.5°	5451.3
5°	5016.0
7.5°	4446.8
10°	3844.1
12.5°	3261.4
15°	2729.0
17.5°	2233.4
20°	1838.3
22.5°	1537.0
25°	1292.5
27.5°	1095.0
30°	897.4
32.5°	696.5
35°	502.3
37.5°	331.5
40°	197.6
42.5°	113.8
45°	56.9
47.5°	20.1
50°	6.7
52.5°	6.7
55°	3.3
57.5°	3.3
60°	3.3
62.5°	3.3
65°	3.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)