

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212272

Luminaire Tested: **LSR4B40D010BZ EC4B30509027 4LBSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212272
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B40D010BZ EC4B30509027 4LBSMW1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3438.7 lumens
Efficiency: N/A
Efficacy: 82.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212272

CATALOG NUMBER: LSR4B40D010BZ EC4B30509027 4LBSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P212272

CATALOG NUMBER: LSR4B40D010BZ EC4B30509027 4LBSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																			
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212272

CATALOG NUMBER: LSR4B40D010BZ EC4B30509027 4LBSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.3	3.8
10°-20°	374.2	10.9
20°-30°	563.6	16.4
30°-40°	670.6	19.5
40°-50°	669.3	19.5
50°-60°	544.3	15.8
60°-70°	334.9	9.7
70°-80°	129.7	3.8
80°-90°	20.8	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1069.0	31.1
0°-40°	1739.6	50.6
0°-60°	2953.3	85.9
0°-90°	3438.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3438.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1386	
5°	1381	131
15°	1328	374
25°	1226	564
35°	1074	671
45°	870	669
55°	609	544
65°	336	335
75°	118	130
85°	16	21
90°	0	



TEST NUMBER: P212272

CATALOG NUMBER: LSR4B40D010BZ EC4B30509027 4LBSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1385.5
2.5°	1387.5
5°	1381.4
7.5°	1373.2
10°	1363.1
12.5°	1344.7
15°	1328.4
17.5°	1304.0
20°	1277.5
22.5°	1253.0
25°	1226.5
27.5°	1189.9
30°	1153.2
32.5°	1118.6
35°	1073.7
37.5°	1024.8
40°	980.0
42.5°	925.0
45°	870.0
47.5°	810.9
50°	747.7
52.5°	682.5
55°	609.2
57.5°	537.9
60°	468.6
62.5°	401.4
65°	336.2
67.5°	275.1
70°	218.0
72.5°	165.0
75°	118.2
77.5°	77.4
80°	46.9
82.5°	28.5
85°	16.3
87.5°	8.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)