

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211427

Luminaire Tested: **LSR4B15D010BZ EC4B10209050 4LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211427
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10209050 4LBSB1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1124.5 lumens
Efficiency: N/A
Efficacy: 78.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211427

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBSB1

Luminous Intensity Polar Plot





TEST NUMBER: P211427

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88		
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76		
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65		
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57		
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50		
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44		
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39		
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35		
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32		
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211427

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.8	4.2
10°-20°	132.8	11.8
20°-30°	197.6	17.6
30°-40°	229.9	20.4
40°-50°	224.1	19.9
50°-60°	172.4	15.3
60°-70°	95.3	8.5
70°-80°	25.3	2.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	377.3	33.5
0°-40°	607.2	54.0
0°-60°	1003.7	89.3
0°-90°	1124.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1124.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	496	
5°	493	47
15°	470	133
25°	429	198
35°	369	230
45°	291	224
55°	192	172
65°	96	95
75°	21	25
85°	0	0
90°	0	



TEST NUMBER: P211427

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBSB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	496.0
2.5°	496.0
5°	493.2
7.5°	488.9
10°	486.1
12.5°	477.5
15°	470.4
17.5°	463.2
20°	453.3
22.5°	443.3
25°	429.0
27.5°	414.8
30°	400.5
32.5°	384.9
35°	369.2
37.5°	349.2
40°	332.1
42.5°	313.6
45°	290.8
47.5°	269.4
50°	245.2
52.5°	219.5
55°	192.4
57.5°	166.8
60°	142.5
62.5°	118.3
65°	95.5
67.5°	74.1
70°	54.2
72.5°	37.1
75°	21.4
77.5°	10.0
80°	1.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)