

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212277

Luminaire Tested: **LSR4B40D010BZ EC4B30509027 4LBWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P212277  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B40D010BZ EC4B30509027 4LBWH1  
Description: PORTFOLIO 4 INCH CYLINDER  
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W  
DL3-44.71W DLE-39.33W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2806.5 lumens  
Efficiency: N/A  
Efficacy: 67.1 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P212277

CATALOG NUMBER: LSR4B40D010BZ EC4B30509027 4LBWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P212277

CATALOG NUMBER: LSR4B40D010BZ EC4B30509027 4LBWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P212277

CATALOG NUMBER: LSR4B40D010BZ EC4B30509027 4LBWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	172.3	6.1
10°-20°	496.4	17.7
20°-30°	732.5	26.1
30°-40°	722.9	25.8
40°-50°	442.4	15.8
50°-60°	169.6	6.0
60°-70°	53.0	1.9
70°-80°	15.5	0.6
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1401.1	49.9
0°-40°	2124.0	75.7
0°-60°	2736.0	97.5
0°-90°	2806.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2806.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1809	
5°	1809	172
15°	1760	496
25°	1603	732
35°	1173	723
45°	567	442
55°	179	170
65°	50	53
75°	15	16
85°	0	2
90°	0	



TEST NUMBER: P212277

CATALOG NUMBER: LSR4B40D010BZ EC4B30509027 4LBWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1809.0
2.5°	1812.8
5°	1809.0
7.5°	1805.2
10°	1793.7
12.5°	1778.5
15°	1759.5
17.5°	1736.6
20°	1702.3
22.5°	1664.3
25°	1603.3
27.5°	1527.1
30°	1431.9
32.5°	1313.9
35°	1173.0
37.5°	1016.8
40°	856.9
42.5°	708.4
45°	567.4
47.5°	441.8
50°	335.1
52.5°	247.5
55°	179.0
57.5°	125.7
60°	91.4
62.5°	68.6
65°	49.5
67.5°	38.1
70°	26.7
72.5°	19.0
75°	15.2
77.5°	7.6
80°	7.6
82.5°	3.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)