

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211435

Luminaire Tested: **LSR4B15D010BZ EC4B10209050 4LBWGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211435
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10209050 4LBWGPH1
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 852.5 lumens
Efficiency: N/A
Efficacy: 59.6 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211435

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBWGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P211435

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBWGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92		
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83		
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	77	76		
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69		
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63		
6	83	72	65	61	81	71	65	60	70	64	60	68	63	59	67	63	59	57		
7	78	67	60	55	76	66	60	55	65	59	55	64	58	55	63	58	54	53		
8	73	62	56	51	72	62	55	51	61	55	51	59	54	50	58	54	50	48		
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45		
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211435

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBWGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.9	6.8
10°-20°	164.0	19.2
20°-30°	235.2	27.6
30°-40°	221.5	26.0
40°-50°	122.3	14.3
50°-60°	39.2	4.6
60°-70°	9.8	1.2
70°-80°	2.4	0.3
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	457.1	53.6
0°-40°	678.6	79.6
0°-60°	840.1	98.5
0°-90°	852.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	852.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	614	
5°	611	58
15°	581	164
25°	516	235
35°	359	221
45°	155	122
55°	40	39
65°	9	10
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P211435

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBWGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	613.6
2.5°	609.1
5°	610.6
7.5°	606.2
10°	598.8
12.5°	591.4
15°	581.0
17.5°	572.2
20°	557.4
22.5°	536.7
25°	516.0
27.5°	487.9
30°	450.9
32.5°	409.5
35°	359.3
37.5°	306.0
40°	251.3
42.5°	201.1
45°	155.2
47.5°	116.8
50°	84.3
52.5°	59.1
55°	39.9
57.5°	26.6
60°	19.2
62.5°	13.3
65°	8.9
67.5°	5.9
70°	4.4
72.5°	3.0
75°	1.5
77.5°	1.5
80°	1.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)