

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211445

Luminaire Tested: **LSR4B20D010BZ EC4B10209024 4LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211445
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B20D010BZ EC4B10209024 4LBMH1
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1100.3 lumens
Efficiency: N/A
Efficacy: 52.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211445

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P211445

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73	73	73	73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67	67	67	67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62	62	62	62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58	58	58	58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54	54	54	54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50	50	50	50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47	47	47	47

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211445

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.4	9.1
10°-20°	263.4	23.9
20°-30°	338.5	30.8
30°-40°	254.6	23.1
40°-50°	102.3	9.3
50°-60°	29.1	2.6
60°-70°	9.2	0.8
70°-80°	2.6	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	702.2	63.8
0°-40°	956.9	87.0
0°-60°	1088.2	98.9
0°-90°	1100.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1100.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1091	
5°	1071	100
15°	940	263
25°	747	338
35°	408	255
45°	126	102
55°	30	29
65°	8	9
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P211445

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBMH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1091.0
2.5°	1084.4
5°	1071.1
7.5°	1046.2
10°	1014.6
12.5°	976.4
15°	939.9
17.5°	898.4
20°	853.6
22.5°	805.4
25°	747.3
27.5°	677.5
30°	596.2
32.5°	504.8
35°	408.5
37.5°	318.8
40°	239.1
42.5°	176.0
45°	126.2
47.5°	86.4
50°	59.8
52.5°	41.5
55°	29.9
57.5°	21.6
60°	16.6
62.5°	11.6
65°	8.3
67.5°	6.6
70°	5.0
72.5°	3.3
75°	1.7
77.5°	1.7
80°	1.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)