

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212326

Luminaire Tested: **LSR4B40D010BZ EC4B30508030 4LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212326
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B40D010BZ EC4B30508030 4LBSB1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3528.6 lumens
Efficiency: N/A
Efficacy: 84.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212326

CATALOG NUMBER: LSR4B40D010BZ EC4B30508030 4LBSB1

Luminous Intensity Polar Plot





TEST NUMBER: P212326

CATALOG NUMBER: LSR4B40D010BZ EC4B30508030 4LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88	88	88	88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76	76	76	76
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65	65	65	65
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57	57	57	57
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50	50	50	50
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44	44	44	44
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39	39	39	39
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35	35	35	35
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32	32	32	32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29	29	29	29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212326

CATALOG NUMBER: LSR4B40D010BZ EC4B30508030 4LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.9	4.2
10°-20°	416.8	11.8
20°-30°	620.1	17.6
30°-40°	721.6	20.4
40°-50°	703.3	19.9
50°-60°	540.9	15.3
60°-70°	299.0	8.5
70°-80°	79.2	2.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1183.8	33.6
0°-40°	1905.4	54.0
0°-60°	3149.7	89.3
0°-90°	3528.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3528.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1557	
5°	1548	147
15°	1476	417
25°	1346	620
35°	1158	722
45°	912	703
55°	604	541
65°	300	299
75°	67	79
85°	0	1
90°	0	



TEST NUMBER: P212326

CATALOG NUMBER: LSR4B40D010BZ EC4B30508030 4LBSB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1556.6
2.5°	1556.6
5°	1547.6
7.5°	1534.2
10°	1525.3
12.5°	1498.4
15°	1476.0
17.5°	1453.7
20°	1422.4
22.5°	1391.1
25°	1346.3
27.5°	1301.6
30°	1256.9
32.5°	1207.7
35°	1158.5
37.5°	1095.9
40°	1042.2
42.5°	984.0
45°	912.5
47.5°	845.4
50°	769.3
52.5°	688.8
55°	603.8
57.5°	523.3
60°	447.3
62.5°	371.2
65°	299.7
67.5°	232.6
70°	170.0
72.5°	116.3
75°	67.1
77.5°	31.3
80°	4.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)