

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212337

Luminaire Tested: **LSR4B40D010BZ EC4B30508030 4LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212337
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B40D010BZ EC4B30508030 4LBWMW1
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3569.9 lumens
Efficiency: N/A
Efficacy: 85.4 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212337

CATALOG NUMBER: LSR4B40D010BZ EC4B30508030 4LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P212337

CATALOG NUMBER: LSR4B40D010BZ EC4B30508030 4LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78		
3	96	87	80	75	93	85	79	74	83	77	73	80	76	72	78	74	71	69		
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61		
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55		
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	60	55	51	50		
7	73	61	53	48	71	60	53	48	59	52	47	57	51	47	56	51	47	45		
8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	61	49	42	37	59	48	41	37	47	41	37	46	41	37	46	40	36	35		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212337

CATALOG NUMBER: LSR4B40D010BZ EC4B30508030 4LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.1	5.7
10°-20°	568.0	15.9
20°-30°	802.7	22.5
30°-40°	777.5	21.8
40°-50°	524.7	14.7
50°-60°	325.6	9.1
60°-70°	217.6	6.1
70°-80°	119.1	3.3
80°-90°	31.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1573.8	44.1
0°-40°	2351.4	65.9
0°-60°	3201.7	89.7
0°-90°	3569.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3569.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2163	
5°	2145	203
15°	2015	568
25°	1760	803
35°	1251	778
45°	672	525
55°	357	326
65°	218	218
75°	111	119
85°	28	32
90°	0	



TEST NUMBER: P212337

CATALOG NUMBER: LSR4B40D010BZ EC4B30508030 4LBWMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2163.2
2.5°	2163.2
5°	2144.7
7.5°	2121.6
10°	2093.8
12.5°	2066.0
15°	2015.0
17.5°	1973.3
20°	1903.8
22.5°	1834.4
25°	1760.2
27.5°	1658.3
30°	1547.2
32.5°	1403.6
35°	1250.7
37.5°	1097.8
40°	945.0
42.5°	792.1
45°	671.7
47.5°	560.5
50°	477.1
52.5°	407.6
55°	356.7
57.5°	315.0
60°	282.6
62.5°	250.1
65°	217.7
67.5°	189.9
70°	162.1
72.5°	139.0
75°	111.2
77.5°	88.0
80°	64.9
82.5°	46.3
85°	27.8
87.5°	9.3
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)