

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211460

Luminaire Tested: **LSR4B20D010BZ EC4B10209024 4LBSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211460
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B20D010BZ EC4B10209024 4LBSMW1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1498.5 lumens
Efficiency: N/A
Efficacy: 72.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211460

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P211460

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																																				
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																																				
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																																				
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																																				
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																																				
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																																				
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																																				
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																																				
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																																				
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211460

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.2	3.8
10°-20°	163.1	10.9
20°-30°	245.6	16.4
30°-40°	292.2	19.5
40°-50°	291.7	19.5
50°-60°	237.2	15.8
60°-70°	145.9	9.7
70°-80°	56.5	3.8
80°-90°	9.1	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	465.9	31.1
0°-40°	758.1	50.6
0°-60°	1287.0	85.9
0°-90°	1498.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1498.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	604	
5°	602	57
15°	579	163
25°	534	246
35°	468	292
45°	379	292
55°	266	237
65°	146	146
75°	52	57
85°	7	9
90°	0	



TEST NUMBER: P211460

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	603.8
2.5°	604.7
5°	602.0
7.5°	598.5
10°	594.0
12.5°	586.0
15°	578.9
17.5°	568.3
20°	556.7
22.5°	546.1
25°	534.5
27.5°	518.5
30°	502.6
32.5°	487.5
35°	467.9
37.5°	446.6
40°	427.1
42.5°	403.1
45°	379.1
47.5°	353.4
50°	325.9
52.5°	297.4
55°	265.5
57.5°	234.4
60°	204.2
62.5°	174.9
65°	146.5
67.5°	119.9
70°	95.0
72.5°	71.9
75°	51.5
77.5°	33.7
80°	20.4
82.5°	12.4
85°	7.1
87.5°	3.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)