

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212354

Luminaire Tested: **LSR4B40D010BZ EC4B30509030 4LBPSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P212354  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B40D010BZ EC4B30509030 4LBPSMW1  
Description: PORTFOLIO 4 INCH CYLINDER  
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM  
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W  
DL3-44.71W DLE-39.33W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3721.9 lumens  
Efficiency: N/A  
Efficacy: 89.0 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P212354

CATALOG NUMBER: LSR4B40D010BZ EC4B30509030 4LBPSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P212354

CATALOG NUMBER: LSR4B40D010BZ EC4B30509030 4LBPSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																			
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P212354

CATALOG NUMBER: LSR4B40D010BZ EC4B30509030 4LBPSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	142.1	3.8
10°-20°	405.0	10.9
20°-30°	610.0	16.4
30°-40°	725.8	19.5
40°-50°	724.5	19.5
50°-60°	589.2	15.8
60°-70°	362.5	9.7
70°-80°	140.4	3.8
80°-90°	22.5	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1157.1	31.1
0°-40°	1882.9	50.6
0°-60°	3196.5	85.9
0°-90°	3721.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3721.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1500	
5°	1495	142
15°	1438	405
25°	1328	610
35°	1162	726
45°	942	724
55°	659	589
65°	364	362
75°	128	140
85°	18	22
90°	0	



TEST NUMBER: P212354

CATALOG NUMBER: LSR4B40D010BZ EC4B30509030 4LBPSMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1499.6
2.5°	1501.8
5°	1495.2
7.5°	1486.3
10°	1475.3
12.5°	1455.5
15°	1437.8
17.5°	1411.4
20°	1382.7
22.5°	1356.2
25°	1327.6
27.5°	1287.9
30°	1248.2
32.5°	1210.7
35°	1162.2
37.5°	1109.2
40°	1060.7
42.5°	1001.2
45°	941.6
47.5°	877.7
50°	809.3
52.5°	738.8
55°	659.4
57.5°	582.2
60°	507.2
62.5°	434.4
65°	363.9
67.5°	297.7
70°	236.0
72.5°	178.6
75°	127.9
77.5°	83.8
80°	50.7
82.5°	30.9
85°	17.6
87.5°	8.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)