

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211546

Luminaire Tested: **LSR4B20D010BZ EC4B10209727 4LBSLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211546  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B20D010BZ EC4B10209727 4LBSLI1  
Description: PORTFOLIO 4 INCH CYLINDER  
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W  
DL3-21.8 6W DLE-22.46W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1481.4 lumens  
Efficiency: N/A  
Efficacy: 71.2 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211546

CATALOG NUMBER: LSR4B20D010BZ EC4B10209727 4LBSLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P211546

CATALOG NUMBER: LSR4B20D010BZ EC4B10209727 4LBSLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90						90													
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80						80													
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71						71													
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63						63													
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57						57													
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51						51													
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46						46													
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42						42													
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39						39													
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36						36													

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211546

CATALOG NUMBER: LSR4B20D010BZ EC4B10209727 4LBSLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.9	6.5
10°-20°	244.6	16.5
20°-30°	317.0	21.4
30°-40°	310.6	21.0
40°-50°	263.2	17.8
50°-60°	172.6	11.6
60°-70°	69.3	4.7
70°-80°	7.9	0.5
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	657.5	44.4
0°-40°	968.1	65.4
0°-60°	1403.9	94.8
0°-90°	1481.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1481.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1058	
5°	1030	96
15°	872	245
25°	692	317
35°	494	311
45°	343	263
55°	192	173
65°	67	69
75°	3	8
85°	0	0
90°	0	



TEST NUMBER: P211546

CATALOG NUMBER: LSR4B20D010BZ EC4B10209727 4LBSLI1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1057.8
2.5°	1049.6
5°	1029.9
7.5°	997.1
10°	956.1
12.5°	911.8
15°	872.5
17.5°	829.8
20°	787.2
22.5°	741.3
25°	692.1
27.5°	641.2
30°	588.8
32.5°	539.6
35°	493.6
37.5°	455.9
40°	414.9
42.5°	378.8
45°	342.8
47.5°	305.0
50°	267.3
52.5°	229.6
55°	191.9
57.5°	157.4
60°	124.6
62.5°	95.1
65°	67.2
67.5°	44.3
70°	26.2
72.5°	11.5
75°	3.3
77.5°	1.6
80°	1.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)