

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212416

Luminaire Tested: **LSR4B40D010BZ EC4B30508035 4LBSLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P212416  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B40D010BZ EC4B30508035 4LBSLI1  
Description: PORTFOLIO 4 INCH CYLINDER  
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W  
DL3-44.71W DLE-39.33W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4290.1 lumens  
Efficiency: N/A  
Efficacy: 102.6 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P212416

CATALOG NUMBER: LSR4B40D010BZ EC4B30508035 4LBSLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P212416

CATALOG NUMBER: LSR4B40D010BZ EC4B30508035 4LBSLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90																			
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80																			
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71																			
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63																			
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57																			
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51																			
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46																			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42																			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39																			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P212416

CATALOG NUMBER: LSR4B40D010BZ EC4B30508035 4LBSLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	277.8	6.5
10°-20°	708.4	16.5
20°-30°	918.0	21.4
30°-40°	899.4	21.0
40°-50°	762.4	17.8
50°-60°	499.7	11.6
60°-70°	200.9	4.7
70°-80°	22.9	0.5
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1904.1	44.4
0°-40°	2803.5	65.3
0°-60°	4065.6	94.8
0°-90°	4290.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4290.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3063	
5°	2983	278
15°	2527	708
25°	2004	918
35°	1430	899
45°	993	762
55°	556	500
65°	195	201
75°	10	23
85°	0	1
90°	0	



TEST NUMBER: P212416

CATALOG NUMBER: LSR4B40D010BZ EC4B30508035 4LBSLI1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3063.3
2.5°	3039.5
5°	2982.6
7.5°	2887.6
10°	2768.8
12.5°	2640.6
15°	2526.6
17.5°	2403.1
20°	2279.7
22.5°	2146.7
25°	2004.2
27.5°	1857.0
30°	1705.0
32.5°	1562.5
35°	1429.5
37.5°	1320.3
40°	1201.6
42.5°	1097.1
45°	992.6
47.5°	883.4
50°	774.1
52.5°	664.9
55°	555.7
57.5°	455.9
60°	360.9
62.5°	275.5
65°	194.7
67.5°	128.2
70°	76.0
72.5°	33.2
75°	9.5
77.5°	4.7
80°	4.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)