

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211613

Luminaire Tested: **LSR4B20D010BZ EC4B10209030 4LBWWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211613  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B20D010BZ EC4B10209030 4LBWWH1  
Description: PORTFOLIO 4 INCH CYLINDER  
WIDE DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W  
DL3-21.8 6W DLE-22.46W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1500.9 lumens  
Efficiency: N/A  
Efficacy: 72.2 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211613

CATALOG NUMBER: LSR4B20D010BZ EC4B10209030 4LBWWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P211613

CATALOG NUMBER: LSR4B20D010BZ EC4B10209030 4LBWWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92																												
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	87	85	84																												
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76																												
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69																												
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63																												
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58																												
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53																												
8	73	62	56	51	72	62	55	51	61	55	51	60	54	50	59	54	50	49																												
9	69	58	51	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45																												
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41																												

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211613

CATALOG NUMBER: LSR4B20D010BZ EC4B10209030 4LBWWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	90.9	6.1
10°-20°	281.3	18.7
20°-30°	432.7	28.8
30°-40°	417.5	27.8
40°-50°	217.7	14.5
50°-60°	45.8	3.1
60°-70°	10.6	0.7
70°-80°	4.1	0.3
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	804.9	53.6
0°-40°	1222.4	81.4
0°-60°	1485.9	99.0
0°-90°	1500.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1500.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	938	
5°	946	91
15°	995	281
25°	948	433
35°	677	417
45°	277	218
55°	41	46
65°	10	11
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P211613

CATALOG NUMBER: LSR4B20D010BZ EC4B10209030 4LBWWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	938.5
2.5°	940.4
5°	946.3
7.5°	954.2
10°	965.9
12.5°	981.7
15°	995.4
17.5°	1003.2
20°	997.4
22.5°	985.6
25°	948.3
27.5°	903.1
30°	844.2
32.5°	765.7
35°	677.3
37.5°	581.1
40°	481.0
42.5°	380.9
45°	276.8
47.5°	186.5
50°	119.8
52.5°	72.6
55°	41.2
57.5°	25.5
60°	17.7
62.5°	13.7
65°	9.8
67.5°	7.9
70°	5.9
72.5°	5.9
75°	3.9
77.5°	2.0
80°	2.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)