

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212433

Luminaire Tested: **LSR4B40D010BZ EC4B30509035 4LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212433
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B40D010BZ EC4B30509035 4LBMMW1
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2771.1 lumens
Efficiency: N/A
Efficacy: 66.3 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212433

CATALOG NUMBER: LSR4B40D010BZ EC4B30509035 4LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P212433

CATALOG NUMBER: LSR4B40D010BZ EC4B30509035 4LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89																			
2	104	98	92	88	102	96	91	87	93	89	85	89	86	83	87	84	81	80																			
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71																			
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	69	66	64																			
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58																			
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53																			
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49																			
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45																			
9	67	55	48	44	66	55	48	44	54	48	44	53	47	43	52	47	43	42																			
10	63	52	45	41	62	51	45	41	51	45	40	50	44	40	49	44	40	39																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212433

CATALOG NUMBER: LSR4B40D010BZ EC4B30509035 4LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.0	7.0
10°-20°	522.7	18.9
20°-30°	695.1	25.1
30°-40°	568.5	20.5
40°-50°	331.1	11.9
50°-60°	219.6	7.9
60°-70°	144.4	5.2
70°-80°	76.2	2.7
80°-90°	18.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1412.8	51.0
0°-40°	1981.2	71.5
0°-60°	2532.0	91.4
0°-90°	2771.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2771.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2104	
5°	2080	195
15°	1863	523
25°	1526	695
35°	907	568
45°	418	331
55°	245	220
65°	144	144
75°	72	76
85°	16	19
90°	0	



TEST NUMBER: P212433

CATALOG NUMBER: LSR4B40D010BZ EC4B30509035 4LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2103.6
2.5°	2099.6
5°	2079.6
7.5°	2031.4
10°	1979.2
12.5°	1931.0
15°	1862.8
17.5°	1786.5
20°	1722.3
22.5°	1633.9
25°	1525.5
27.5°	1409.1
30°	1260.6
32.5°	1083.9
35°	907.3
37.5°	746.7
40°	606.2
42.5°	497.8
45°	417.5
47.5°	353.3
50°	309.1
52.5°	273.0
55°	244.9
57.5°	216.8
60°	188.7
62.5°	168.6
65°	144.5
67.5°	124.5
70°	104.4
72.5°	88.3
75°	72.3
77.5°	56.2
80°	40.1
82.5°	28.1
85°	16.1
87.5°	4.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)