

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211619

Luminaire Tested: **LSR4B20D010BZ EC4B10209730 4LBMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211619  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B20D010BZ EC4B10209730 4LBMH1  
Description: PORTFOLIO 4 INCH CYLINDER  
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W  
DL3-21.8 6W DLE-22.46W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1136.8 lumens  
Efficiency: N/A  
Efficacy: 54.7 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211619

CATALOG NUMBER: LSR4B20D010BZ EC4B10209730 4LBMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P211619

CATALOG NUMBER: LSR4B20D010BZ EC4B10209730 4LBMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85																			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79																			
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73																			
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67																			
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62																			
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58																			
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54																			
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50																			
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211619

CATALOG NUMBER: LSR4B20D010BZ EC4B10209730 4LBMH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	103.7	9.1
10°-20°	272.1	23.9
20°-30°	349.7	30.8
30°-40°	263.1	23.1
40°-50°	105.7	9.3
50°-60°	30.0	2.6
60°-70°	9.5	0.8
70°-80°	2.7	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	725.5	63.8
0°-40°	988.7	87.0
0°-60°	1124.4	98.9
0°-90°	1136.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1136.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1127	
5°	1107	104
15°	971	272
25°	772	350
35°	422	263
45°	130	106
55°	31	30
65°	9	10
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P211619

CATALOG NUMBER: LSR4B20D010BZ EC4B10209730 4LBMH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1127.2
2.5°	1120.4
5°	1106.6
7.5°	1080.9
10°	1048.3
12.5°	1008.8
15°	971.1
17.5°	928.2
20°	881.9
22.5°	832.1
25°	772.1
27.5°	700.0
30°	615.9
32.5°	521.6
35°	422.1
37.5°	329.4
40°	247.1
42.5°	181.9
45°	130.4
47.5°	89.2
50°	61.8
52.5°	42.9
55°	30.9
57.5°	22.3
60°	17.2
62.5°	12.0
65°	8.6
67.5°	6.9
70°	5.1
72.5°	3.4
75°	1.7
77.5°	1.7
80°	1.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)