

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211658

Luminaire Tested: **LSR4B20D010BZ EC4B10208035 4LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211658
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B20D010BZ EC4B10208035 4LBPSMW1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2212.7 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211658

CATALOG NUMBER: LSR4B20D010BZ EC4B10208035 4LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P211658

CATALOG NUMBER: LSR4B20D010BZ EC4B10208035 4LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																			
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211658

CATALOG NUMBER: LSR4B20D010BZ EC4B10208035 4LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.5	3.8
10°-20°	240.8	10.9
20°-30°	362.6	16.4
30°-40°	431.5	19.5
40°-50°	430.7	19.5
50°-60°	350.3	15.8
60°-70°	215.5	9.7
70°-80°	83.5	3.8
80°-90°	13.4	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	687.9	31.1
0°-40°	1119.4	50.6
0°-60°	1900.3	85.9
0°-90°	2212.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2212.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	892	
5°	889	84
15°	855	241
25°	789	363
35°	691	431
45°	560	431
55°	392	350
65°	216	215
75°	76	83
85°	10	13
90°	0	



TEST NUMBER: P211658

CATALOG NUMBER: LSR4B20D010BZ EC4B10208035 4LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	891.5
2.5°	892.8
5°	888.9
7.5°	883.6
10°	877.1
12.5°	865.3
15°	854.8
17.5°	839.1
20°	822.0
22.5°	806.3
25°	789.2
27.5°	765.6
30°	742.0
32.5°	719.8
35°	690.9
37.5°	659.4
40°	630.6
42.5°	595.2
45°	559.8
47.5°	521.8
50°	481.1
52.5°	439.2
55°	392.0
57.5°	346.1
60°	301.5
62.5°	258.3
65°	216.3
67.5°	177.0
70°	140.3
72.5°	106.2
75°	76.0
77.5°	49.8
80°	30.2
82.5°	18.4
85°	10.5
87.5°	5.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)