

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212472

Luminaire Tested: **LSR4B40D010BZ EC4B30508040 4LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212472
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B40D010BZ EC4B30508040 4LBSGPH1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3815.2 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212472

CATALOG NUMBER: LSR4B40D010BZ EC4B30508040 4LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P212472

CATALOG NUMBER: LSR4B40D010BZ EC4B30508040 4LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88			88
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			76
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66			66
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57			57
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50			50
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45			45
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40			40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36			36
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32			32
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30			30

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212472

CATALOG NUMBER: LSR4B40D010BZ EC4B30508040 4LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.8	4.4
10°-20°	468.3	12.3
20°-30°	683.0	17.9
30°-40°	778.9	20.4
40°-50°	747.1	19.6
50°-60°	572.2	15.0
60°-70°	314.0	8.2
70°-80°	83.5	2.2
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1318.1	34.5
0°-40°	2097.0	55.0
0°-60°	3416.4	89.5
0°-90°	3815.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3815.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1772	
5°	1758	167
15°	1662	468
25°	1484	683
35°	1245	779
45°	971	747
55°	641	572
65°	316	314
75°	73	84
85°	0	1
90°	0	



TEST NUMBER: P212472

CATALOG NUMBER: LSR4B40D010BZ EC4B30508040 4LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1771.9
2.5°	1767.3
5°	1758.2
7.5°	1744.4
10°	1726.1
12.5°	1694.1
15°	1662.0
17.5°	1625.4
20°	1584.2
22.5°	1533.8
25°	1483.5
27.5°	1433.1
30°	1369.0
32.5°	1309.5
35°	1245.4
37.5°	1181.3
40°	1117.2
42.5°	1048.5
45°	970.7
47.5°	892.8
50°	810.4
52.5°	723.4
55°	641.0
57.5°	558.6
60°	471.6
62.5°	389.2
65°	315.9
67.5°	242.7
70°	178.6
72.5°	119.0
75°	73.3
77.5°	32.1
80°	9.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)