

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211674

Luminaire Tested: **LSR4B20D010BZ EC4B10209035 4LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211674
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B20D010BZ EC4B10209035 4LBCSMW1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1830.7 lumens
Efficiency: N/A
Efficacy: 88.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211674

CATALOG NUMBER: LSR4B20D010BZ EC4B10209035 4LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P211674

CATALOG NUMBER: LSR4B20D010BZ EC4B10209035 4LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87			87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74			74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63			63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55			55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48			48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42			42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37			37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33			33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30			30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27			27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211674

CATALOG NUMBER: LSR4B20D010BZ EC4B10209035 4LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.8	3.9
10°-20°	201.7	11.0
20°-30°	303.4	16.6
30°-40°	359.6	19.6
40°-50°	357.8	19.5
50°-60°	288.5	15.8
60°-70°	174.5	9.5
70°-80°	64.8	3.5
80°-90°	9.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	575.9	31.5
0°-40°	935.5	51.1
0°-60°	1581.8	86.4
0°-90°	1830.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1830.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	748	
5°	744	71
15°	714	202
25°	659	303
35°	576	360
45°	466	358
55°	322	288
65°	175	175
75°	59	65
85°	8	10
90°	0	



TEST NUMBER: P211674

CATALOG NUMBER: LSR4B20D010BZ EC4B10209035 4LBCSMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	747.7
2.5°	747.7
5°	744.4
7.5°	742.2
10°	735.5
12.5°	724.4
15°	714.4
17.5°	703.4
20°	690.0
22.5°	676.7
25°	659.0
27.5°	640.1
30°	619.0
32.5°	599.1
35°	575.8
37.5°	551.4
40°	522.5
42.5°	494.8
45°	465.9
47.5°	433.8
50°	398.3
52.5°	361.7
55°	321.7
57.5°	286.2
60°	246.3
62.5°	210.8
65°	175.3
67.5°	142.0
70°	110.9
72.5°	83.2
75°	58.8
77.5°	37.7
80°	22.2
82.5°	13.3
85°	7.8
87.5°	3.3
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)