

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212476

Luminaire Tested: **LSR4B40D010BZ EC4B30508040 4LBSWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P212476  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B40D010BZ EC4B30508040 4LBSWH1  
Description: PORTFOLIO 4 INCH CYLINDER  
SHALLOW DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W  
DL3-44.71W DLE-39.33W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4181.1 lumens  
Efficiency: N/A  
Efficacy: 100.0 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P212476

CATALOG NUMBER: LSR4B40D010BZ EC4B30508040 4LBSWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P212476

CATALOG NUMBER: LSR4B40D010BZ EC4B30508040 4LBSWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89																			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77																			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67																			
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59																			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52																			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47																			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42																			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38																			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35																			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P212476

CATALOG NUMBER: LSR4B40D010BZ EC4B30508040 4LBSWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	230.0	5.5
10°-20°	595.3	14.2
20°-30°	778.6	18.6
30°-40°	824.5	19.7
40°-50°	769.0	18.4
50°-60°	582.4	13.9
60°-70°	315.4	7.5
70°-80°	84.6	2.0
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1603.9	38.4
0°-40°	2428.4	58.1
0°-60°	3779.8	90.4
0°-90°	4181.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4181.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2494	
5°	2457	230
15°	2128	595
25°	1693	779
35°	1318	824
45°	1002	769
55°	654	582
65°	316	315
75°	73	85
85°	0	1
90°	0	



TEST NUMBER: P212476

CATALOG NUMBER: LSR4B40D010BZ EC4B30508040 4LBSWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2493.6
2.5°	2484.4
5°	2457.0
7.5°	2397.5
10°	2319.7
12.5°	2228.2
15°	2127.5
17.5°	2013.1
20°	1912.5
22.5°	1798.1
25°	1692.9
27.5°	1587.6
30°	1487.0
32.5°	1400.1
35°	1317.7
37.5°	1235.3
40°	1157.6
42.5°	1079.8
45°	1002.0
47.5°	915.1
50°	828.1
52.5°	741.2
55°	654.3
57.5°	562.8
60°	475.8
62.5°	393.5
65°	315.7
67.5°	242.5
70°	178.4
72.5°	123.5
75°	73.2
77.5°	32.0
80°	9.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)