

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211691

Luminaire Tested: **LSR4B20D010BZ EC4B10209035 4LBSLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211691  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B20D010BZ EC4B10209035 4LBSLI1  
Description: PORTFOLIO 4 INCH CYLINDER  
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W  
DL3-21.8 6W DLE-22.46W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1797.0 lumens  
Efficiency: N/A  
Efficacy: 86.4 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211691

CATALOG NUMBER: LSR4B20D010BZ EC4B10209035 4LBSLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P211691

CATALOG NUMBER: LSR4B20D010BZ EC4B10209035 4LBSLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90																			
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80																			
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71																			
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63																			
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57																			
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51																			
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46																			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42																			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39																			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211691

CATALOG NUMBER: LSR4B20D010BZ EC4B10209035 4LBSLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	116.3	6.5
10°-20°	296.7	16.5
20°-30°	384.5	21.4
30°-40°	376.7	21.0
40°-50°	319.3	17.8
50°-60°	209.3	11.6
60°-70°	84.2	4.7
70°-80°	9.6	0.5
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	797.6	44.4
0°-40°	1174.3	65.3
0°-60°	1703.0	94.8
0°-90°	1797.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1797.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1283	
5°	1249	116
15°	1058	297
25°	840	385
35°	599	377
45°	416	319
55°	233	209
65°	82	84
75°	4	10
85°	0	0
90°	0	



TEST NUMBER: P211691

CATALOG NUMBER: LSR4B20D010BZ EC4B10209035 4LBSLI1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1283.1
2.5°	1273.1
5°	1249.3
7.5°	1209.5
10°	1159.8
12.5°	1106.0
15°	1058.3
17.5°	1006.6
20°	954.9
22.5°	899.2
25°	839.5
27.5°	777.8
30°	714.2
32.5°	654.5
35°	598.8
37.5°	553.0
40°	503.3
42.5°	459.5
45°	415.8
47.5°	370.0
50°	324.3
52.5°	278.5
55°	232.7
57.5°	191.0
60°	151.2
62.5°	115.4
65°	81.6
67.5°	53.7
70°	31.8
72.5°	13.9
75°	4.0
77.5°	2.0
80°	2.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)