

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211694

Luminaire Tested: **LSR4B20D010BZ EC4B10209035 4LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211694
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B20D010BZ EC4B10209035 4LBSWMH1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1747.0 lumens
Efficiency: N/A
Efficacy: 84.0 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211694

CATALOG NUMBER: LSR4B20D010BZ EC4B10209035 4LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P211694

CATALOG NUMBER: LSR4B20D010BZ EC4B10209035 4LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90		
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	82	76	94	87	81	76	84	79	74	81	77	73	79	75	72	70		
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62		
5	83	73	65	59	82	72	64	59	70	63	59	68	62	58	66	61	57	56		
6	78	66	59	53	76	65	58	53	64	57	53	62	57	52	61	56	52	50		
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45		
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41		
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	49	43	39	38		
10	60	48	41	37	59	48	41	37	47	41	36	46	40	36	45	40	36	35		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211694

CATALOG NUMBER: LSR4B20D010BZ EC4B10209035 4LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.3	5.9
10°-20°	271.2	15.5
20°-30°	364.2	20.8
30°-40°	372.8	21.3
40°-50°	322.7	18.5
50°-60°	214.7	12.3
60°-70°	88.2	5.0
70°-80°	10.5	0.6
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	737.7	42.2
0°-40°	1110.6	63.6
0°-60°	1647.9	94.3
0°-90°	1747.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1747.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1107	
5°	1090	102
15°	969	271
25°	795	364
35°	595	373
45°	420	323
55°	238	215
65°	87	88
75°	5	10
85°	0	0
90°	0	



TEST NUMBER: P211694

CATALOG NUMBER: LSR4B20D010BZ EC4B10209035 4LBSWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1107.2
2.5°	1104.9
5°	1090.0
7.5°	1067.1
10°	1036.2
12.5°	1001.9
15°	968.7
17.5°	926.3
20°	885.1
22.5°	841.6
25°	794.6
27.5°	744.3
30°	693.9
32.5°	643.5
35°	595.4
37.5°	549.6
40°	506.1
42.5°	462.6
45°	420.2
47.5°	375.6
50°	329.8
52.5°	284.0
55°	238.2
57.5°	198.1
60°	156.9
62.5°	119.1
65°	87.0
67.5°	57.3
70°	33.2
72.5°	16.0
75°	4.6
77.5°	2.3
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)