

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212515

Luminaire Tested: **LSR4B40D010BZ EC4B30508050 4LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212515
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B40D010BZ EC4B30508050 4LBCSMW1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4415.5 lumens
Efficiency: N/A
Efficacy: 105.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212515

CATALOG NUMBER: LSR4B40D010BZ EC4B30508050 4LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P212515

CATALOG NUMBER: LSR4B40D010BZ EC4B30508050 4LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87																			
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74																			
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63																			
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55																			
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48																			
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42																			
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37																			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33																			
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30																			
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212515

CATALOG NUMBER: LSR4B40D010BZ EC4B30508050 4LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.9	3.9
10°-20°	486.4	11.0
20°-30°	731.8	16.6
30°-40°	867.2	19.6
40°-50°	863.0	19.5
50°-60°	695.7	15.8
60°-70°	420.9	9.5
70°-80°	156.3	3.5
80°-90°	23.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1389.1	31.5
0°-40°	2256.3	51.1
0°-60°	3815.0	86.4
0°-90°	4415.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4415.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1803	
5°	1795	171
15°	1723	486
25°	1589	732
35°	1389	867
45°	1124	863
55°	776	696
65°	423	421
75°	142	156
85°	19	23
90°	0	



TEST NUMBER: P212515

CATALOG NUMBER: LSR4B40D010BZ EC4B30508050 4LBCSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1803.4
2.5°	1803.4
5°	1795.4
7.5°	1790.0
10°	1774.0
12.5°	1747.2
15°	1723.1
17.5°	1696.4
20°	1664.3
22.5°	1632.2
25°	1589.4
27.5°	1543.9
30°	1493.0
32.5°	1444.9
35°	1388.7
37.5°	1329.8
40°	1260.2
42.5°	1193.4
45°	1123.8
47.5°	1046.2
50°	960.6
52.5°	872.3
55°	775.9
57.5°	690.3
60°	594.0
62.5°	508.4
65°	422.8
67.5°	342.5
70°	267.6
72.5°	200.7
75°	141.8
77.5°	91.0
80°	53.5
82.5°	32.1
85°	18.7
87.5°	8.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)