

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212533

Luminaire Tested: **LSR4B40D010BZ EC4B30508050 4LBSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P212533  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B40D010BZ EC4B30508050 4LBSMW1  
Description: PORTFOLIO 4 INCH CYLINDER  
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W  
DL3-44.71W DLE-39.33W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4334.1 lumens  
Efficiency: N/A  
Efficacy: 103.7 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P212533

CATALOG NUMBER: LSR4B40D010BZ EC4B30508050 4LBSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P212533

CATALOG NUMBER: LSR4B40D010BZ EC4B30508050 4LBSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																			
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P212533

CATALOG NUMBER: LSR4B40D010BZ EC4B30508050 4LBSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	165.5	3.8
10°-20°	471.6	10.9
20°-30°	710.3	16.4
30°-40°	845.2	19.5
40°-50°	843.6	19.5
50°-60°	686.1	15.8
60°-70°	422.1	9.7
70°-80°	163.5	3.8
80°-90°	26.2	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1347.4	31.1
0°-40°	2192.6	50.6
0°-60°	3722.3	85.9
0°-90°	4334.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4334.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1746	
5°	1741	165
15°	1674	472
25°	1546	710
35°	1353	845
45°	1096	844
55°	768	686
65°	424	422
75°	149	164
85°	20	26
90°	0	



TEST NUMBER: P212533

CATALOG NUMBER: LSR4B40D010BZ EC4B30508050 4LBSMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1746.2
2.5°	1748.8
5°	1741.1
7.5°	1730.8
10°	1718.0
12.5°	1694.9
15°	1674.3
17.5°	1643.5
20°	1610.1
22.5°	1579.3
25°	1545.9
27.5°	1499.7
30°	1453.5
32.5°	1409.8
35°	1353.3
37.5°	1291.7
40°	1235.2
42.5°	1165.9
45°	1096.5
47.5°	1022.0
50°	942.4
52.5°	860.3
55°	767.8
57.5°	677.9
60°	590.6
62.5°	505.9
65°	423.7
67.5°	346.7
70°	274.8
72.5°	208.0
75°	148.9
77.5°	97.6
80°	59.1
82.5°	36.0
85°	20.5
87.5°	10.3
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)