

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212542

Luminaire Tested: **LSR4B40D010BZ EC4B30509050 4LBCSMB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P212542  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B40D010BZ EC4B30509050 4LBCSMB1  
Description: PORTFOLIO 4 INCH CYLINDER  
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM  
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W  
DL3-44.71W DLE-39.33W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3480.7 lumens  
Efficiency: N/A  
Efficacy: 83.3 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P212542

CATALOG NUMBER: LSR4B40D010BZ EC4B30509050 4LBCSMB1

### Luminous Intensity Polar Plot





TEST NUMBER: P212542

CATALOG NUMBER: LSR4B40D010BZ EC4B30509050 4LBCSMB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88	88	88	88
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75	75	75	75
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65	65	65	65
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56	56	56	56
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49	49	49	49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43	43	43	43
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39	39	39	39
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35	35	35	35
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31	31	31	31
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28	28	28	28

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P212542

CATALOG NUMBER: LSR4B40D010BZ EC4B30509050 4LBCSMB1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.0	4.0
10°-20°	396.0	11.4
20°-30°	595.4	17.1
30°-40°	706.4	20.3
40°-50°	699.1	20.1
50°-60°	549.1	15.8
60°-70°	307.8	8.8
70°-80°	86.5	2.5
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1130.4	32.5
0°-40°	1836.8	52.8
0°-60°	3085.0	88.6
0°-90°	3480.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3480.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1470	
5°	1467	139
15°	1405	396
25°	1293	595
35°	1133	706
45°	911	699
55°	619	549
65°	307	308
75°	75	86
85°	0	1
90°	0	



TEST NUMBER: P212542

CATALOG NUMBER: LSR4B40D010BZ EC4B30509050 4LBCSMB1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1469.7
2.5°	1464.7
5°	1467.2
7.5°	1454.8
10°	1439.8
12.5°	1422.3
15°	1404.9
17.5°	1382.4
20°	1352.5
22.5°	1322.5
25°	1292.6
27.5°	1260.1
30°	1217.7
32.5°	1175.3
35°	1132.9
37.5°	1083.0
40°	1025.6
42.5°	970.7
45°	910.8
47.5°	843.4
50°	773.5
52.5°	693.7
55°	618.8
57.5°	534.0
60°	454.1
62.5°	381.8
65°	306.9
67.5°	242.0
70°	179.7
72.5°	122.3
75°	74.9
77.5°	37.4
80°	10.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)