

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212547

Luminaire Tested: **LSR4B40D010BZ EC4B30509050 4LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212547
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B40D010BZ EC4B30509050 4LBMH1
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2678.8 lumens
Efficiency: N/A
Efficacy: 64.1 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212547

CATALOG NUMBER: LSR4B40D010BZ EC4B30509050 4LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P212547

CATALOG NUMBER: LSR4B40D010BZ EC4B30509050 4LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73	73	73	73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67	67	67	67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62	62	62	62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58	58	58	58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54	54	54	54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50	50	50	50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47	47	47	47

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212547

CATALOG NUMBER: LSR4B40D010BZ EC4B30509050 4LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	244.4	9.1
10°-20°	641.2	23.9
20°-30°	824.1	30.8
30°-40°	620.0	23.1
40°-50°	249.0	9.3
50°-60°	70.8	2.6
60°-70°	22.4	0.8
70°-80°	6.4	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1709.7	63.8
0°-40°	2329.7	87.0
0°-60°	2649.5	98.9
0°-90°	2678.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2678.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2656	
5°	2608	244
15°	2288	641
25°	1819	824
35°	995	620
45°	307	249
55°	73	71
65°	20	22
75°	4	6
85°	0	1
90°	0	



TEST NUMBER: P212547

CATALOG NUMBER: LSR4B40D010BZ EC4B30509050 4LBMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2656.3
2.5°	2640.1
5°	2607.8
7.5°	2547.1
10°	2470.3
12.5°	2377.3
15°	2288.4
17.5°	2187.3
20°	2078.1
22.5°	1960.9
25°	1819.4
27.5°	1649.6
30°	1451.4
32.5°	1229.1
35°	994.6
37.5°	776.3
40°	582.2
42.5°	428.6
45°	307.3
47.5°	210.2
50°	145.5
52.5°	101.1
55°	72.8
57.5°	52.6
60°	40.4
62.5°	28.3
65°	20.2
67.5°	16.2
70°	12.1
72.5°	8.1
75°	4.0
77.5°	4.0
80°	4.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)