

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212554

Luminaire Tested: **LSR4B40D010BZ EC4B30509050 4LBNI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212554
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B40D010BZ EC4B30509050 4LBNI1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2622.2 lumens
Efficiency: N/A
Efficacy: 62.7 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212554

CATALOG NUMBER: LSR4B40D010BZ EC4B30509050 4LBNLI1

Luminous Intensity Polar Plot





TEST NUMBER: P212554

CATALOG NUMBER: LSR4B40D010BZ EC4B30509050 4LBNLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90	90	90	90
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85	85	85	85
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	81	81
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77	77	77	77
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69	69	69	69
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66	66	66	66
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63	63	63	63
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61	61	61	61

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212554

CATALOG NUMBER: LSR4B40D010BZ EC4B30509050 4LBNLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	531.8	20.3
10°-20°	910.4	34.7
20°-30°	723.6	27.6
30°-40°	383.0	14.6
40°-50°	66.0	2.5
50°-60°	4.9	0.2
60°-70°	2.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2165.8	82.6
0°-40°	2548.8	97.2
0°-60°	2619.8	99.9
0°-90°	2622.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2622.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6748	
5°	6050	532
15°	3291	910
25°	1559	724
35°	606	383
45°	69	66
55°	4	5
65°	4	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P212554

CATALOG NUMBER: LSR4B40D010BZ EC4B30509050 4LBNLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	6748.2
2.5°	6574.6
5°	6049.6
7.5°	5363.0
10°	4636.1
12.5°	3933.4
15°	3291.3
17.5°	2693.6
20°	2217.1
22.5°	1853.6
25°	1558.8
27.5°	1320.6
30°	1082.3
32.5°	840.0
35°	605.8
37.5°	399.8
40°	238.3
42.5°	137.3
45°	68.7
47.5°	24.2
50°	8.1
52.5°	8.1
55°	4.0
57.5°	4.0
60°	4.0
62.5°	4.0
65°	4.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)