

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211770

Luminaire Tested: **LSR4B20D010BZ EC4B10208050 4LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211770
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B20D010BZ EC4B10208050 4LBNH1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1310.4 lumens
Efficiency: N/A
Efficacy: 63.0 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211770

CATALOG NUMBER: LSR4B20D010BZ EC4B10208050 4LBNH1

Luminous Intensity Polar Plot





TEST NUMBER: P211770

CATALOG NUMBER: LSR4B20D010BZ EC4B10208050 4LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93		
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87		
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81		
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75		
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70		
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65		
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61		
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58		
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54		
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211770

CATALOG NUMBER: LSR4B20D010BZ EC4B10208050 4LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.4	11.3
10°-20°	360.1	27.5
20°-30°	418.1	31.9
30°-40°	276.8	21.1
40°-50°	77.6	5.9
50°-60°	19.5	1.5
60°-70°	7.3	0.6
70°-80°	2.5	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	926.6	70.7
0°-40°	1203.4	91.8
0°-60°	1300.6	99.3
0°-90°	1310.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1310.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1645	
5°	1603	148
15°	1289	360
25°	916	418
35°	444	277
45°	90	78
55°	21	20
65°	7	7
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P211770

CATALOG NUMBER: LSR4B20D010BZ EC4B10208050 4LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1645.3
2.5°	1638.2
5°	1602.6
7.5°	1540.8
10°	1464.9
12.5°	1379.4
15°	1289.2
17.5°	1201.3
20°	1104.0
22.5°	1013.8
25°	916.4
27.5°	823.8
30°	705.1
32.5°	579.3
35°	444.0
37.5°	318.1
40°	216.0
42.5°	140.1
45°	90.2
47.5°	54.6
50°	35.6
52.5°	26.1
55°	21.4
57.5°	16.6
60°	11.9
62.5°	9.5
65°	7.1
67.5°	4.7
70°	4.7
72.5°	2.4
75°	2.4
77.5°	2.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)