

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P430991

Luminaire Tested: **LAMR4B112R309024DE010x1MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P430991
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-8)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B112R309024DE010x1MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 30 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1057.3 lumens
Efficiency: N/A
Efficacy: 73.9 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P430991

CATALOG NUMBER: LAMR4B112R309024DE010x1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P430991

CATALOG NUMBER: LAMR4B112R309024DE010x1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	100	99	98	96	96	96	96	96	96	96	96	96	96	96	96	96															
2	111	107	104	102	109	106	103	100	102	100	98	96	94	92	91	90	88	86	84	82	80	78	76	74	72	70	68	66	64	62															
3	107	103	99	96	105	101	98	95	99	96	94	92	90	88	86	84	82	80	78	76	74	72	70	68	66	64	62	60	58	56															
4	104	98	94	91	102	97	94	91	95	92	90	88	86	84	82	80	78	76	74	72	70	68	66	64	62	60	58	56	54	52															
5	101	95	91	87	99	94	90	87	92	89	86	84	82	80	78	76	74	72	70	68	66	64	62	60	58	56	54	52	50	48															
6	98	91	87	84	97	91	87	84	89	86	83	81	79	77	75	73	71	69	67	65	63	61	59	57	55	53	51	49	47	45															
7	95	88	84	81	94	88	84	81	87	83	81	79	77	75	73	71	69	67	65	63	61	59	57	55	53	51	49	47	45	43															
8	92	86	81	79	91	85	81	78	84	81	78	76	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40															
9	90	83	79	76	89	83	79	76	82	78	76	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40	38															
10	88	81	77	74	87	80	77	74	80	76	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40	38	36															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1915743
5°	1873882
10°	1624763
15°	1007011
20°	369106
25°	123357
30°	60560
35°	30175
40°	18742
45°	11862
50°	8443
55°	6881
60°	5921
65°	4670
70°	5770
75°	5719
80°	5683
85°	5661



TEST NUMBER: P430991

CATALOG NUMBER: LAMR4B112R309024DE010x1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	344.8	32.6
10°-20°	520.6	49.2
20°-30°	126.9	12.0
30°-40°	34.8	3.3
40°-50°	14.0	1.3
50°-60°	7.5	0.7
60°-70°	4.5	0.4
70°-80°	3.4	0.3
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	992.4	93.9
0°-40°	1027.1	97.1
0°-60°	1048.6	99.2
0°-90°	1057.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1057.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3883	
5°	3784	345
15°	1972	521
25°	227	127
35°	50	35
45°	17	14
55°	8	7
65°	4	4
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P430991

CATALOG NUMBER: LAMR4B112R309024DE010x1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	3882.9
2.5°	3856.8
5°	3783.6
7.5°	3609.1
10°	3243.1
12.5°	2669.5
15°	1971.5
17.5°	1270.6
20°	703.0
22.5°	375.1
25°	226.6
27.5°	153.4
30°	106.3
32.5°	72.2
35°	50.1
37.5°	37.1
40°	29.1
42.5°	22.1
45°	17.0
47.5°	14.0
50°	11.0
52.5°	10.0
55°	8.0
57.5°	7.0
60°	6.0
62.5°	5.0
65°	4.0
67.5°	4.0
70°	4.0
72.5°	4.0
75°	3.0
77.5°	3.0
80°	2.0
82.5°	1.0
85°	1.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)