

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211833

Luminaire Tested: **LSR4B30D010BZ EC4B30509024 4LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211833
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30509024 4LBSB1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1820.4 lumens
Efficiency: N/A
Efficacy: 65.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211833

CATALOG NUMBER: LSR4B30D010BZ EC4B30509024 4LBSB1

Luminous Intensity Polar Plot





TEST NUMBER: P211833

CATALOG NUMBER: LSR4B30D010BZ EC4B30509024 4LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88																			
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76																			
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65																			
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57																			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50																			
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44																			
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39																			
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35																			
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32																			
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211833

CATALOG NUMBER: LSR4B30D010BZ EC4B30509024 4LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.8	4.2
10°-20°	215.0	11.8
20°-30°	319.9	17.6
30°-40°	372.3	20.4
40°-50°	362.8	19.9
50°-60°	279.1	15.3
60°-70°	154.3	8.5
70°-80°	40.9	2.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	610.7	33.5
0°-40°	983.0	54.0
0°-60°	1624.9	89.3
0°-90°	1820.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1820.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	803	
5°	798	76
15°	762	215
25°	695	320
35°	598	372
45°	471	363
55°	312	279
65°	155	154
75°	35	41
85°	0	0
90°	0	



TEST NUMBER: P211833

CATALOG NUMBER: LSR4B30D010BZ EC4B30509024 4LBSB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	803.0
2.5°	803.0
5°	798.4
7.5°	791.5
10°	786.9
12.5°	773.0
15°	761.5
17.5°	749.9
20°	733.8
22.5°	717.6
25°	694.6
27.5°	671.5
30°	648.4
32.5°	623.0
35°	597.7
37.5°	565.3
40°	537.7
42.5°	507.7
45°	470.7
47.5°	436.1
50°	396.9
52.5°	355.4
55°	311.5
57.5°	270.0
60°	230.8
62.5°	191.5
65°	154.6
67.5°	120.0
70°	87.7
72.5°	60.0
75°	34.6
77.5°	16.2
80°	2.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)