

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211858

Luminaire Tested: **LSR4B30D010BZ EC4B30508027 4LBNI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211858
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30508027 4LBNI1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2054.9 lumens
Efficiency: N/A
Efficacy: 73.4 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211858

CATALOG NUMBER: LSR4B30D010BZ EC4B30508027 4LBNLI1

Luminous Intensity Polar Plot





TEST NUMBER: P211858

CATALOG NUMBER: LSR4B30D010BZ EC4B30508027 4LBNLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95																																				
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90																																				
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85																																				
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81																																				
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77																																				
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73																																				
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69																																				
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66																																				
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63																																				
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211858

CATALOG NUMBER: LSR4B30D010BZ EC4B30508027 4LBNLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	416.7	20.3
10°-20°	713.5	34.7
20°-30°	567.0	27.6
30°-40°	300.1	14.6
40°-50°	51.7	2.5
50°-60°	3.9	0.2
60°-70°	2.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1697.2	82.6
0°-40°	1997.4	97.2
0°-60°	2052.9	99.9
0°-90°	2054.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2054.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5288	
5°	4741	417
15°	2579	713
25°	1222	567
35°	475	300
45°	54	52
55°	3	4
65°	3	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P211858

CATALOG NUMBER: LSR4B30D010BZ EC4B30508027 4LBNLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	5288.1
2.5°	5152.0
5°	4740.6
7.5°	4202.6
10°	3633.0
12.5°	3082.4
15°	2579.2
17.5°	2110.8
20°	1737.4
22.5°	1452.6
25°	1221.6
27.5°	1034.8
30°	848.1
32.5°	658.2
35°	474.7
37.5°	313.3
40°	186.7
42.5°	107.6
45°	53.8
47.5°	19.0
50°	6.3
52.5°	6.3
55°	3.2
57.5°	3.2
60°	3.2
62.5°	3.2
65°	3.2
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)