

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211880

Luminaire Tested: **LSR4B30D010BZ EC4B30509027 4LBMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211880  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B30D010BZ EC4B30509027 4LBMH1  
Description: PORTFOLIO 4 INCH CYLINDER  
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1802.5 lumens  
Efficiency: N/A  
Efficacy: 64.4 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211880

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P211880

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73	73	73	73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67	67	67	67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62	62	62	62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58	58	58	58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54	54	54	54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50	50	50	50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47	47	47	47

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211880

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBMH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	164.5	9.1
10°-20°	431.5	23.9
20°-30°	554.5	30.8
30°-40°	417.2	23.1
40°-50°	167.6	9.3
50°-60°	47.6	2.6
60°-70°	15.1	0.8
70°-80°	4.3	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1150.4	63.8
0°-40°	1567.6	87.0
0°-60°	1782.8	98.9
0°-90°	1802.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1802.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1787	
5°	1755	164
15°	1540	431
25°	1224	554
35°	669	417
45°	207	168
55°	49	48
65°	14	15
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P211880

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBMH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1787.3
2.5°	1776.5
5°	1754.7
7.5°	1713.9
10°	1662.2
12.5°	1599.6
15°	1539.8
17.5°	1471.8
20°	1398.3
22.5°	1319.4
25°	1224.2
27.5°	1109.9
30°	976.6
32.5°	827.0
35°	669.2
37.5°	522.3
40°	391.7
42.5°	288.4
45°	206.8
47.5°	141.5
50°	97.9
52.5°	68.0
55°	49.0
57.5°	35.4
60°	27.2
62.5°	19.0
65°	13.6
67.5°	10.9
70°	8.2
72.5°	5.4
75°	2.7
77.5°	2.7
80°	2.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)