

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211892

Luminaire Tested: **LSR4B30D010BZ EC4B30509027 4LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211892
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30509027 4LBSGPH1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2159.8 lumens
Efficiency: N/A
Efficacy: 77.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211892

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P211892

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211892

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.4	4.4
10°-20°	265.1	12.3
20°-30°	386.7	17.9
30°-40°	440.9	20.4
40°-50°	423.0	19.6
50°-60°	323.9	15.0
60°-70°	177.8	8.2
70°-80°	47.3	2.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	746.2	34.5
0°-40°	1187.2	55.0
0°-60°	1934.1	89.5
0°-90°	2159.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2159.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1003	
5°	995	94
15°	941	265
25°	840	387
35°	705	441
45°	550	423
55°	363	324
65°	179	178
75°	42	47
85°	0	1
90°	0	



TEST NUMBER: P211892

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1003.1
2.5°	1000.5
5°	995.4
7.5°	987.6
10°	977.2
12.5°	959.1
15°	940.9
17.5°	920.2
20°	896.9
22.5°	868.3
25°	839.8
27.5°	811.3
30°	775.0
32.5°	741.3
35°	705.0
37.5°	668.8
40°	632.5
42.5°	593.6
45°	549.5
47.5°	505.5
50°	458.8
52.5°	409.5
55°	362.9
57.5°	316.2
60°	267.0
62.5°	220.3
65°	178.9
67.5°	137.4
70°	101.1
72.5°	67.4
75°	41.5
77.5°	18.1
80°	5.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)