

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P429846

Luminaire Tested: **LAM4B112R309030DE010x1MW**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P429846
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-8)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B112R309030DE010x1MW
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 30 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1198.6 lumens
Efficiency: N/A
Efficacy: 83.8 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P429846

CATALOG NUMBER: LAM4B112R309030DE010x1MW

Luminous Intensity Polar Plot





TEST NUMBER: P429846

CATALOG NUMBER: LAM4B112R309030DE010x1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	390.9	32.6
10°-20°	590.2	49.2
20°-30°	143.9	12.0
30°-40°	39.4	3.3
40°-50°	15.9	1.3
50°-60°	8.5	0.7
60°-70°	5.0	0.4
70°-80°	3.9	0.3
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1125.0	93.9
0°-40°	1164.4	97.1
0°-60°	1188.8	99.2
0°-90°	1198.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1198.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4402	
5°	4289	391
15°	2235	590
25°	257	144
35°	57	39
45°	19	16
55°	9	9
65°	4	5
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P429846

CATALOG NUMBER: LAM4B112R309030DE010x1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4401.9
2.5°	4372.3
5°	4289.3
7.5°	4091.5
10°	3676.6
12.5°	3026.3
15°	2235.0
17.5°	1440.4
20°	796.9
22.5°	425.2
25°	256.9
27.5°	173.9
30°	120.5
32.5°	81.9
35°	56.8
37.5°	42.1
40°	33.0
42.5°	25.0
45°	19.3
47.5°	15.9
50°	12.5
52.5°	11.4
55°	9.1
57.5°	8.0
60°	6.8
62.5°	5.7
65°	4.5
67.5°	4.5
70°	4.5
72.5°	4.5
75°	3.4
77.5°	3.4
80°	2.3
82.5°	1.1
85°	1.1
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)