

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211893

Luminaire Tested: **LSR4B30D010BZ EC4B30509027 4LBSH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211893
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30509027 4LBSH1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2354.1 lumens
Efficiency: N/A
Efficacy: 84.1 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211893

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBSH1

Luminous Intensity Polar Plot





TEST NUMBER: P211893

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBSH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211893

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBSH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.3	4.9
10°-20°	313.4	13.3
20°-30°	435.3	18.5
30°-40°	475.0	20.2
40°-50°	443.1	18.8
50°-60°	336.3	14.3
60°-70°	184.2	7.8
70°-80°	50.7	2.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	864.1	36.7
0°-40°	1339.1	56.9
0°-60°	2118.5	90.0
0°-90°	2354.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2354.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1231	
5°	1221	115
15°	1117	313
25°	946	435
35°	759	475
45°	575	443
55°	376	336
65°	184	184
75°	44	51
85°	0	1
90°	0	



TEST NUMBER: P211893

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBSH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1231.2
2.5°	1231.2
5°	1220.8
7.5°	1205.3
10°	1181.9
12.5°	1150.8
15°	1117.1
17.5°	1075.7
20°	1036.8
22.5°	990.1
25°	946.1
27.5°	902.0
30°	852.7
32.5°	806.1
35°	759.4
37.5°	712.8
40°	668.7
42.5°	622.1
45°	575.4
47.5°	528.8
50°	476.9
52.5°	427.7
55°	375.8
57.5°	326.6
60°	277.3
62.5°	228.1
65°	184.0
67.5°	142.6
70°	106.3
72.5°	72.6
75°	44.1
77.5°	20.7
80°	5.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)