

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P430998

Luminaire Tested: **LAMR4B112R309030DE010x1MW**

Issue Date: 11/23/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P430998  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-8)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 11/23/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LAMR4B112R309030DE010x1MW  
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 30 DEG TIR OPTIC  
Light Source: HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1198.6 lumens  
Efficiency: N/A  
Efficacy: 83.8 lumens/watt  
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P430998

CATALOG NUMBER: LAMR4B112R309030DE010x1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P430998

CATALOG NUMBER: LAMR4B112R309030DE010x1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	100	99	98	96	96	96	96																
2	111	107	104	102	109	106	103	100	102	100	98	100	98	96	97	95	94	93	93	93	93																
3	107	103	99	96	105	101	98	95	99	96	94	96	94	92	94	92	91	90	90	90	90																
4	104	98	94	91	102	97	94	91	95	92	90	93	91	89	92	90	88	87	87	87	87																
5	101	95	91	87	99	94	90	87	92	89	86	91	88	86	89	87	85	84	84	84	84																
6	98	91	87	84	97	91	87	84	89	86	83	88	85	83	87	84	82	81	81	81	81																
7	95	88	84	81	94	88	84	81	87	83	81	86	83	80	85	82	80	79	79	79	79																
8	92	86	81	79	91	85	81	78	84	81	78	83	80	78	83	80	78	77	77	77	77																
9	90	83	79	76	89	83	79	76	82	78	76	81	78	76	80	78	75	74	74	74	74																
10	88	81	77	74	87	80	77	74	80	76	74	79	76	74	78	76	73	72	72	72	72																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2171807
5°	2124337
10°	1841942
15°	1141602
20°	418407
25°	139852
30°	68650
35°	34211
40°	21254
45°	13466
50°	9595
55°	7828
60°	6710
65°	5253
70°	6491
75°	6481
80°	6535
85°	6227



TEST NUMBER: P430998

CATALOG NUMBER: LAMR4B112R309030DE010x1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	390.9	32.6
10°-20°	590.2	49.2
20°-30°	143.9	12.0
30°-40°	39.4	3.3
40°-50°	15.9	1.3
50°-60°	8.5	0.7
60°-70°	5.0	0.4
70°-80°	3.9	0.3
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1125.0	93.9
0°-40°	1164.4	97.1
0°-60°	1188.8	99.2
0°-90°	1198.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1198.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4402	
5°	4289	391
15°	2235	590
25°	257	144
35°	57	39
45°	19	16
55°	9	9
65°	4	5
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P430998

CATALOG NUMBER: LAMR4B112R309030DE010x1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4401.9
2.5°	4372.3
5°	4289.3
7.5°	4091.5
10°	3676.6
12.5°	3026.3
15°	2235.0
17.5°	1440.4
20°	796.9
22.5°	425.2
25°	256.9
27.5°	173.9
30°	120.5
32.5°	81.9
35°	56.8
37.5°	42.1
40°	33.0
42.5°	25.0
45°	19.3
47.5°	15.9
50°	12.5
52.5°	11.4
55°	9.1
57.5°	8.0
60°	6.8
62.5°	5.7
65°	4.5
67.5°	4.5
70°	4.5
72.5°	4.5
75°	3.4
77.5°	3.4
80°	2.3
82.5°	1.1
85°	1.1
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)