

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P431070

Luminaire Tested: **LAMR4B112R459030DE010x1MW**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P431070
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2008-908-8)
Test Lab: INNOVATION CENTER (G2)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B112R459030DE010x1MW
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 45 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1186.3 lumens
Efficiency: N/A
Efficacy: 83.0 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.66
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P431070

CATALOG NUMBER: LAMR4B112R459030DE010x1MW

Luminous Intensity Polar Plot





TEST NUMBER: P431070

CATALOG NUMBER: LAMR4B112R459030DE010x1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89	89	89	89
3	105	99	94	91	103	98	93	90	95	92	89	93	90	87	90	88	86	85	85	85	85
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80	80	80	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76	76	76	76
6	92	85	79	76	91	84	79	75	82	78	75	81	77	74	80	77	74	73	73	73	73
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69	69	69	69
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66	66	66	66
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	65	63	63	63	63
10	79	71	66	62	78	70	66	62	70	65	62	69	65	62	68	65	62	61	61	61	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1096191
5°	1095822
10°	1041560
15°	914916
20°	699936
25°	408615
30°	167266
35°	70711
40°	38579
45°	24909
50°	19419
55°	16860
60°	13617
65°	10740
70°	9954
75°	8769
80°	9944
85°	6793



TEST NUMBER: P431070

CATALOG NUMBER: LAMR4B112R459030DE010x1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.0	17.5
10°-20°	487.7	41.1
20°-30°	343.6	29.0
30°-40°	84.6	7.1
40°-50°	29.5	2.5
50°-60°	17.5	1.5
60°-70°	9.7	0.8
70°-80°	5.3	0.4
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1038.3	87.5
0°-40°	1122.9	94.7
0°-60°	1169.8	98.6
0°-90°	1186.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1186.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2222	
5°	2213	207
15°	1791	488
25°	751	344
35°	117	85
45°	36	29
55°	20	17
65°	9	10
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P431070

CATALOG NUMBER: LAMR4B112R459030DE010x1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2221.8
2.5°	2216.0
5°	2212.6
7.5°	2172.3
10°	2079.0
12.5°	1952.4
15°	1791.2
17.5°	1582.9
20°	1333.1
22.5°	1046.4
25°	750.6
27.5°	484.6
30°	293.6
32.5°	178.4
35°	117.4
37.5°	82.9
40°	59.9
42.5°	46.0
45°	35.7
47.5°	29.9
50°	25.3
52.5°	21.9
55°	19.6
57.5°	17.3
60°	13.8
62.5°	11.5
65°	9.2
67.5°	8.1
70°	6.9
72.5°	5.8
75°	4.6
77.5°	4.6
80°	3.5
82.5°	2.3
85°	1.2
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)