

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211976

Luminaire Tested: **LSR4B30D010BZ EC4B30509030 4LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211976
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30509030 4LBNWH1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1636.7 lumens
Efficiency: N/A
Efficacy: 58.5 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.62
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211976

CATALOG NUMBER: LSR4B30D010BZ EC4B30509030 4LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P211976

CATALOG NUMBER: LSR4B30D010BZ EC4B30509030 4LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95																												
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89																												
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84																												
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79																												
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75																												
6	91	83	78	74	90	82	77	74	81	76	73	79	76	73	78	75	72	71																												
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67																												
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64																												
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61																												
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	58																												

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211976

CATALOG NUMBER: LSR4B30D010BZ EC4B30509030 4LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	284.4	17.4
10°-20°	533.6	32.6
20°-30°	478.7	29.3
30°-40°	274.7	16.8
40°-50°	54.8	3.3
50°-60°	6.9	0.4
60°-70°	3.1	0.2
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1296.7	79.2
0°-40°	1571.4	96.0
0°-60°	1633.2	99.8
0°-90°	1636.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1636.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3478	
5°	3199	284
15°	1916	534
25°	1034	479
35°	435	275
45°	59	55
55°	8	7
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P211976

CATALOG NUMBER: LSR4B30D010BZ EC4B30509030 4LBNWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3478.3
2.5°	3407.7
5°	3198.6
7.5°	2893.4
10°	2560.0
12.5°	2232.2
15°	1915.8
17.5°	1638.9
20°	1401.5
22.5°	1203.7
25°	1034.2
27.5°	898.5
30°	748.8
32.5°	596.2
35°	435.1
37.5°	296.7
40°	183.7
42.5°	110.2
45°	59.3
47.5°	25.4
50°	11.3
52.5°	8.5
55°	8.5
57.5°	5.7
60°	5.7
62.5°	2.8
65°	2.8
67.5°	2.8
70°	2.8
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)